



- NOTES:
- 1. ASSEMBLY KIT TO BE BULK PACKED.
 - 2. CONTACTS TO BE INSERTED INTO CABLE CONNECTOR.

NOTE: DAISY CHAIN GROMMET SET CONTAINS
(3) SIZES Ø0.125, Ø0.188 & Ø0.250




ASS'Y. PART NO.	CONTACT QTY.	GROMMET SIZE		
8282-2SG-3DC	2-#20	DAISY CHAIN		
8282-3SG-3DC	3-#20	DAISY CHAIN		
8282-4SG-3DC	4-#20	DAISY CHAIN		
8282-5SG-3DC	5-#20	DAISY CHAIN		
8282-6SG-3DC	6-#20	DAISY CHAIN		
8282-2SG-3XX	2-#20	SINGLE GROMMET		
8282-3SG-3XX	3-#20	SINGLE GROMMET		
8282-4SG-3XX	4-#20	SINGLE GROMMET		
8282-5SG-3XX	5-#20	SINGLE GROMMET		
8282-6SG-3XX	6-#20	SINGLE GROMMET		
8282-SG-3				

GROMMET SIZE
NUMBER OF CONTACTS



CUSTOMER APPROVAL

CHECKED BY: _____
APPROVED BY: _____
DATE: _____



A	RCS	6-2-03	DRAWING CREATED PER DOR #03-9004SS	
REV.	INIT.	DATE	DESCRIPTION	
ALL INFORMATION ILLUSTRATED IS THE PROPERTY OF "CONZALL CORPORATION." UNAUTHORIZED DUPLICATION OR DISTRIBUTION OF THIS DOCUMENT IS PROHIBITED.			ORIG. DRAWN BY: RCS	DATE: 5-29-03
ALL UNITS ARE IN FEET, INCHES, FRACTION OF INCHES AND DECIMALS. UNLESS OTHERWISE SPECIFIED TOLERANCES: 3 PLACE DECIMALS ±.005 ANGLES ±1° FRACTIONS ±1/16			CHECKED BY:	
= CRITICAL CHARACTERISTIC FLAG PER SPEC. XXXX			APPROVED BY:	
SCALE	SIZE	SHEET	TITLE: CONNECTOR ASSEMBLY #20 SOCKET CONTACT MINI-CON-X	
NTS	B	1 OF 1	CUSTOMER: STANDARD PRODUCT	
FILE:	DIRECTORY:	PART NUMBER:	REV. A	
8282XSG3XX	CATALOG	8282-XSG-3XX		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Switchcraft:

[8282-6SG-3DC](#) [8282-5SG-3DC](#) [8282-3SG-3DC](#) [8282-4SG-3DC](#) [8282-2SG-3DC](#) [8282-2SG-311](#) [8282-2SG-315](#)
[8282-2SG-318](#) [8282-2SG-321](#) [8282-2SG-3XX](#) [8282-3SG-311](#) [8282-3SG-315](#) [8282-3SG-318](#) [8282-3SG-321](#) [8282-](#)
[3SG-3XX](#) [8282-4SG-311](#) [8282-4SG-315](#) [8282-4SG-318](#) [8282-4SG-321](#) [8282-4SG-3XX](#) [8282-5SG-311](#) [8282-5SG-](#)
[315](#) [8282-5SG-318](#) [8282-5SG-321](#) [8282-5SG-3XX](#) [8282-6SG-311](#) [8282-6SG-315](#) [8282-6SG-318](#) [8282-6SG-321](#)
[8282-6SG-3XX](#)