



Product: [MDVO 6-PORT MULTIMEDIA BOX](#)

6-Port MDVO Multimedia Outlet Box

Product Description

MDVO 6-Port Multimedia Box is available in many colors.

Technical Specifications

Physical Characteristics (Overall)

Height:	1.5 m
Width:	6.3
Depth:	7.4
Port Count:	6 Port
Front Connection:	Flush
Packaging:	Individually packaged cardboard box
Weight:	0.7 kg

Connectors

Materials

Material
Plastic - UL94V-0

Temperature Range

Installation Temperature Range:	-10 to 60°C
Storage Temperature Range:	-40 to 70°C
Operating Temperature Range:	-10 to 60°C

Mechanical Characteristics

Footprint/Type:	MDVO
-----------------	------

Applicable Environmental and Other Programs

Environmental Space:	Indoor
EU Directive 2002/95/EC (RoHS):	Yes
MII Order #39 (China RoHS):	EUP 50

Flammability, LS0H, Toxicity Testing

Safety Listing:	c(UL)us Listed
-----------------	----------------

Related Part Numbers

Related Parts:	Compatible with 10GX, CAT6+ and CAT5E MDVO UTP and fiber Modules
----------------	--

Variants

Item #	Color	Port Count
A0643206	Almond	6 Port
A0643208	Black	6 Port
A0643205	Grey	6 Port

AX102595	Ivory	6 Port
A0643207	White	6 Port

Product Notes

Included Parts:	Screws, Cable tie, MDVO Blank, Instruction sheet, Bezels for SC Duplex adaptors
Notes:	For proper installation refer to the installation guide PX106468 included with the product or visit our web site at http://www.belden.com

History

Update and Revision:	Revision Number: 0.177 Revision Date: 03-04-2023
----------------------	--

© 2023 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.