

# HC-STA-B32-HHFD-1STP42-EL-AL - Housing

1424835

<https://www.phoenixcontact.com/us/products/1424835>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sleeve housing B32, for double locking latch, material: Die-cast aluminum, salt water resistant, cable outlets: 1, lateral, 1x Pg42, height: 94 mm, cable gland: none, Standard

## Your advantages

- Good shielding in the event of electromagnetic interference

## Commercial data

Item number	1424835
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BF56
Product key	BF7APB
Catalog page	Page 644 (C-2-2019)
GTIN	4055626382401
Weight per piece (including packing)	417.6 g
Weight per piece (excluding packing)	417.6 g
Customs tariff number	85389099
Country of origin	CN

## Technical data


### Product properties

Product type	Housing with locking latch
Housing type	Sleeve housing
Application	Standard
Type	B32
No. of cable outlets	1
Type of the screw connection	1x Pg42
Type	Tall design
Cable outlet	lateral
Pg screw connection	none

### Data management status

Article revision	01
------------------	----

### Dimensions

Dimensional drawing	
	
Width	82.5 mm
Height	94 mm
Length	94 mm

### Material specifications

Housing material	Die-cast aluminum, salt water resistant
Housing surface material	uncoated

### Mechanical properties

Mechanical data	
Type of the screw connection	1x Pg42
Locking type	Pin

### Environmental and real-life conditions

Ambient conditions	
Degree of protection	IP66
	IP67
Enclosure rating (NEMA)	4 (UL 50e)
	4X (UL 50e)
	12 (UL 50e)
Impact strength	IK09

# HC-STA-B32-HHFD-1STP42-EL-AL - Housing

1424835

<https://www.phoenixcontact.com/us/products/1424835>



Ambient temperature (operation)

-40 °C ... 125 °C

# HC-STA-B32-HHFD-1STP42-EL-AL - Housing


1424835

<https://www.phoenixcontact.com/us/products/1424835>



## Drawings

Dimensional drawing



Dimensional drawing

# HC-STA-B32-HHFD-1STP42-EL-AL - Housing

1424835

<https://www.phoenixcontact.com/us/products/1424835>



## Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1424835>

**DNV**

Approval ID: TAE000037S



**cUL Recognized**

Approval ID: E255026



**UL Recognized**

Approval ID: E255026



**EAC**

Approval ID: RU C-DE.BL08.B.00511

**cULus Recognized**

## Classifications

### ECLASS

ECLASS-11.0	27440202
ECLASS-12.0	27440202
ECLASS-13.0	27440202

### ETIM

ETIM 9.0	EC000437
----------	----------

### UNSPSC

UNSPSC 21.0	31261500
-------------	----------

# HC-STA-B32-HHFD-1STP42-EL-AL - Housing

1424835

<https://www.phoenixcontact.com/us/products/1424835>



## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2024 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)