

# RC-06P1N121500 - Cable connector



1593083

<https://www.phoenixcontact.com/us/products/1593083>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



M23, Cable connector, series: RC, straight, shielded: no, Screw locking mechanism, No. of pos.: 6, Direction of rotation: Standard, contact connection type: Pin, Solder cup, coding: N, Alternative product in accordance with RoHS II without Exemption 6c (Pb < 0.1 %) item no.: 1240323

## Commercial data

Item number	1593083
Packing unit	20 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	AB31
Product key	ABRAFA
GTIN	4046356194174
Weight per piece (including packing)	84.755 g
Weight per piece (excluding packing)	80.6 g
Customs tariff number	85366990
Country of origin	DE

# RC-06P1N121500 - Cable connector



1593083

<https://www.phoenixcontact.com/us/products/1593083>

## Technical data

### Product properties

Product type	Circular connector (cable-side)
--------------	---------------------------------

### Connector

Insulating body	
Coding	N
Insertion/withdrawal cycles	50
Connection method	Solder cup
Contact switching type	Pin
Application	Signal
Number of positions	6
Direction of rotation	Standard
Connection profile	6
Litz wire cross-section <b>Power contacts</b> min.	0.08 mm²
Litz wire cross-section <b>Power contacts</b> max.	2.5 mm²
Rated current <b>Power contacts</b>	20 A
Rated voltage	48 V AC
	74 V DC
Rated surge voltage	1.5 kV
Overvoltage category	III
Degree of pollution	3

### Housing

Housing material	Metal
Type of locking	Screw locking mechanism
Pg screw connection	Pg9
Degree of protection (plugged in)	IP65
	IP67
	IP68
Thread type	M23

# RC-06P1N121500 - Cable connector


1593083

<https://www.phoenixcontact.com/us/products/1593083>



## Drawings

Schematic diagram



Connector pin assignment

# RC-06P1N121500 - Cable connector



1593083

<https://www.phoenixcontact.com/us/products/1593083>

## Classifications

### ECLASS

ECLASS-11.0	27440102
ECLASS-12.0	27440116
ECLASS-13.0	27440116

### ETIM

ETIM 9.0	EC002635
----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# RC-06P1N121500 - Cable connector



1593083  
<https://www.phoenixcontact.com/us/products/1593083>

## Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)
China RoHS	
Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.
EU REACH SVHC	
REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	fb80f4f1-6775-4967-b0d6-5e68ef74e8e1

Phoenix Contact 2024 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)