


AX106631 Faceplates and Panels - Angular MediaFlex Faceplate Kit for KeyConnect Modules, Single-gang



For more Information
please call

1-800-Belden1

General Description:

Angular MediaFlex KeyConnect Single-Gang Faceplate Kit 2-Port, Angled

Usage (Overall)

Suitable Applications:	- Compatible with a variety of modules that are suitable for use with Belden IBDN Systems 10GX, 4800, 3600, 2400 and 1200.
Related Parts:	- Compatible with 10GX, CAT6+ and CAT5E KeyConnect Modular Jacks and KeyConnect Multimedia Modules

Physical Characteristics (Connectivity)

Capacity

Max. Capacity:	2 ports
----------------	---------

Access

Front Connection:	Angled
-------------------	--------

Dimensions

Dimensions:

Height (in.)	Width (in.)	Depth (in.)
4.500	2.750	0.820

Materials

Materials:

Description	Material
Faceplate	High-impact Thermoplastic, flame-retardant UL94V-0, UV-resistant
Insert	High-impact Thermoplastic, flame-retardant UL94V-0, UV-resistant

Color

Color:	Elec. White
--------	-------------

Weight

Weight:	0.106 lbs.
---------	------------

Included Parts

Included Parts:	windows, papers, 6-32 screws, 2-port insert, 1U & 2U blank inserts, blank, installation guide
-----------------	---

Packaging

Packaging:	Individually packaged in a suitable plastic bag
------------	---

Mechanical Characteristics (Connectivity)

Footprint/Type:	KeyConnect
Connector/Hardware Retention:	20 lbs.
Storage Temperature Range:	-40°C To +70°C
Installation Temperature Range:	-10°C To +60°C
Operating Temperature Range:	-10°C To +60°C

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

EU Directive 2011/65/EU (ROHS II):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	01/01/2013

ENGLISH MEASUREMENT VERSION

AX106631 Faceplates and Panels - Angular MediaFlex Faceplate Kit for KeyConnect Modules, Single-gang

MII Order #39 (China RoHS):

EUP 50

Suitability

Suitability - Indoor:

Yes

Transmission Characteristics (Connectivity)**Notes (Overall)****Notes:** For proper installation refer to Installation Guide PX106224 included with the product or visit our web site at <http://www.belden.com>**Product Family****Part Numbers:**

Description	Gray	Almond	Elec White	Black
Angular MediaFlex KeyConnect Single-Gang Faceplate Kit 2-Port, Flush	AX106617	AX106618	AX106619	AX106620
Angular MediaFlex KeyConnect Single-Gang Faceplate Kit 4-Port, Flush	AX106621	AX106622	AX106623	AX106624
Angular MediaFlex KeyConnect Single-Gang Faceplate Kit 6-Port, Flush	AX106625	AX106626	AX106627	AX106628
Angular MediaFlex KeyConnect Single-Gang Faceplate Kit 2-Port, Angled	AX106629	AX106630	AX106631	AX106632
Angular MediaFlex KeyConnect Single-Gang Faceplate Kit 4-Port, Angled	AX106633	AX106634	AX106635	AX106636

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
AX106631	1 EA	0.000 KG			KCONN ANG MFLEX KIT 2P ELW

Revision Number: 0 Revision Date: 10-14-2015

© 2016 Belden, Inc.
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.