

**HDC enclosures**  
**HDC 48B TSLU 1M32G****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings.

The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact.

The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening.

The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned.

Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection.

**General ordering data**

| Type       | HDC 48B TSLU 1M32G                                                                                                                                           |
|------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Order No.  | <a href="#">1788320000</a>                                                                                                                                   |
| Version    | HDC enclosures, Size: 12, Protection degree: IP65, Cable entry from side, Plug housing, End-locking clamp, lower side, Standard, Size of cable entries: M 32 |
| GTIN (EAN) | 4032248205851                                                                                                                                                |
| Qty.       | 1 pc(s).                                                                                                                                                     |

## HDC enclosures

### HDC 48B TSLU 1M32G

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

## Technical data

### Dimensions and weights

|            |        |                 |            |
|------------|--------|-----------------|------------|
| Length     | 151 mm | Length (inches) | 5.945 inch |
| Width      | 90 mm  | Width (inches)  | 3.543 inch |
| Height     | 94 mm  | Height (inches) | 3.701 inch |
| Net weight | 731 g  |                 |            |

### Temperatures

|                   |                   |
|-------------------|-------------------|
| Limit temperature | -40 °C ... 125 °C |
|-------------------|-------------------|

### Environmental Product Compliance

|            |                |
|------------|----------------|
| REACH SVHC | Lead 7439-92-1 |
|------------|----------------|

### Dimensions

|                      |              |                     |       |
|----------------------|--------------|---------------------|-------|
| Cable entry          | w. threading | Height of housing B | 94 mm |
| Total length housing | 132 mm       | Width housing C     | 90 mm |

### General data

|                             |                             |                       |                   |
|-----------------------------|-----------------------------|-----------------------|-------------------|
| EMC housings                | No                          | Housing main material | diecast aluminium |
| Material of locking element | Stainless steel, rust-proof | Protection degree     | IP65              |
| Surface finish              | Powder coating              |                       |                   |

### Version

|                              |                               |                                |                                     |
|------------------------------|-------------------------------|--------------------------------|-------------------------------------|
| Cable entry                  | w. threading                  | Clamp version                  | End-locking clamp                   |
| Design                       | Standard                      | Design of housing              | Cable entry from side, Plug housing |
| Design of locking system     | End-locking clamp, lower side | Internal thread                | M 32                                |
| Number of cable entry on top | 0                             | Number of cable entry sideways | 1                                   |
| Size                         | 12                            | Size of cable entries          | M 32                                |
| Suitable for ModuPlug®       | Yes                           | Top part/bottom part/lid       | upper part                          |
| Type                         | Plug                          |                                |                                     |

### Classifications

|            |             |            |             |
|------------|-------------|------------|-------------|
| ETIM 3.0   | EC000437    | ETIM 4.0   | EC000437    |
| ETIM 5.0   | EC000437    | ETIM 6.0   | EC000437    |
| UNSPSC     | 30-21-18-01 | eClass 5.1 | 27-14-34-19 |
| eClass 6.2 | 27-26-12-03 | eClass 7.1 | 27-44-02-02 |
| eClass 8.1 | 27-44-02-02 | eClass 9.0 | 27-44-02-02 |
| eClass 9.1 | 27-44-02-02 |            |             |

### Approvals

Approvals



|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

### HDC enclosures HDC 48B TSLU 1M32G

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Downloads

|                         |                                                                         |
|-------------------------|-------------------------------------------------------------------------|
| Brochure/Catalogue      | <a href="#">CAT 3 HDC 17/18 EN</a><br><a href="#">FL FIELDWIRING EN</a> |
| Engineering Data        | <a href="#">EPLAN, WSCAD</a>                                            |
| Technical Documentation | <a href="#">1788320000 HDC 48B TSLU 1M32G STP Blatt 1.pdf</a>           |

### HDC enclosures HDC 48B TSLU 1M32G

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

## Drawings

