


90325 - **26	26	36.80	31.75	35.35	37.26
90325 - **24	24	34.26	29.21	32.81	34.72
90325 - **22	22	31.72	26.67	30.27	32.18
90325 - **20	20	29.18	24.13	27.73	29.64
90325 - **18	18	26.64	21.59	25.19	27.10
90325 - **16	16	24.10	19.05	22.65	24.56
90325 - **14	14	21.56	16.51	20.11	22.02
90325 - **12	12	19.02	13.97	17.57	19.48
90325 - **10	10	16.48	11.43	15.03	16.94
90325 - **08	08	13.94	8.89	12.49	14.40
90325 - **06	06	11.40	6.35	9.95	11.86
90325 - **04	04	8.86	3.81	7.41	9.32
PART NO.	NO. OF CKTS	DIM. A	DIM. B	DIM. C	DIM. D



CIRCUIT NO. 1


90325 - * * * *

CIRCUIT SIZE 04 CKT TO 26 CKT
0 = HOUSING: COLOUR BLACK
9 = HOUSING: CUSTOMER SPECIFIC (COLOUR BLACK)

0 = 3 -5µm TIN ASSY
3 = 0.76µm GOLD ASSY
5 = NON STANDARD VOIDED OPTIONSEE SHEET 2 TUBED
6 = ROUND PEG WITH KINKSOPTION SEE SHEET 3 (OBSOLETE)
7 = 0.76µm GOLD ASSY, TUBED
9 = 3-5µm TIN ASSY TUBED

- NOTES:
- HOUSING MATL. POLYESTER PBT 15% GLASS FILLED TO UL94V-0
 - TER. MATL. BRALL 0.28 THK
PLATING. :UNDERPLATED 1.27µm MIN NICKEL
3-5µm TIN SELECTIVE
0.76µm MIN. SELECTIVE GOLD
 - CONFIRMS TO PRODUCT SPECIFICATION PS-99020-0011
 - PACKAGING SPECIFICATION: PK-90325-001

PCB LAYOUT VIEWED FROM SOLDER SIDE.
BOARD 1.60±0.14 THK




INSPECTION NUMBERS USED ON SHEET 1: 1-20
LAST INSPECTION NUMBER USED: 9

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION													
SYMBOLS		DIMENSION UNITS		SCALE		CURRENT REV DESC:				molex HEADER ASSEMBLY			
▽ = 0		mm		5:1		EC NO: 738955 DRWN: GOWTHP 2023/02/02 CHK'D: GOWTHP 2023/02/16 APPR: ISHWARG 2023/02/20 INITIAL REVISION: DRWN: RFC_PLMIMP 2018/10/14 APPR: MWILHITE 2000/07/24							
▽ = 0		GENERAL TOLERANCES (UNLESS SPECIFIED)											
▽ = 0		ANGULAR TOL ± 0.5 °											
▽ = 0		4 PLACES ±						PRODUCT CUSTOMER DRAWING					
▽ = 0		3 PLACES ±						DOCUMENT NUMBER		DOC TYPE		DOC PART	REVISION
▽ = 0		2 PLACES ± 0.2						SDA-90325		PSD		001	AU1
▽ = 0		1 PLACE ± 0.2											
☒ = 0		0 PLACES ±											
■ = 0		DRAFT WHERE APPLICABLE		THIRD ANGLE PROJECTION		DRAWING		SERIES		MATERIAL NUMBER		CUSTOMER	
▽ = 0		MUST REMAIN WITHIN DIMENSIONS				A3-SIZE		90325		SEE TABLE		GENERAL MARKET	
												SHEET NUMBER	
												1 OF 2	

DRAWING REMASTERED TO NX

PART NUMBER OPTIONS ON
SHEET'S 2 & 3 ARE OBSOLETE
AND THEREFORE HAVE BEEN
REMOVED FROM DRAWING.



THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION											
SYMBOLS		DIMENSION UNITS		SCALE		CURRENT REV DESC:				molex	
	= 0	mm		1:1						HEADER ASSEMBLY	
	= 0	GENERAL TOLERANCES (UNLESS SPECIFIED)				EC NO: 738955 DRWN: GOWTHP 2023/02/02 CHK'D: GOWTHP 2023/02/16 APPR: ISHWARG 2023/02/20				PRODUCT CUSTOMER DRAWING	
	= 0										
	= 0	ANGULAR TOL ± 0.5 °				INITIAL REVISION: DRWN: RFC_PLMIMP 2018/10/14 APPR: MWILHITE 2000/07/24				DOCUMENT NUMBER SDA-90325	
	= 0	4 PLACES ±									
	= 0	3 PLACES ±				DOC PART 001					
	= 0	2 PLACES ± 0.2						REVISION AU1			
	= 0	1 PLACE ± 0.2				SHEET NUMBER 2 OF 2					
	= 0	0 PLACES ±									
	= 0	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION		DRAWING		SERIES	
	= 0							A3-SIZE		90325	
	= 0					MATERIAL NUMBER		CUSTOMER			
						SEE TABLE		GENERAL MARKET			