



Part Number : [334722502](#)
Product Description : MX150 Mat-Sealed Female Connector Assembly, Dual Row, 20 Circuits, Keying Option B, with Clipslot, without Connector Position Assurance, Light Gray
Series Number : 33472
Status : Active
Product Category : Connector Housings



Documents & Resources

Drawings
[Drawing 334722502_sd.pdf](#)

3D Models and Design Files
[3D Model 334722502_stp.zip](#)

Specifications
[Application Specification AS-33472-100-CH-001.pdf](#)
[Application Specification AS-33611-001-001.pdf](#)
[Test Summary TS-33472-0001-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant
China RoHS	Not Relevant
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)4144-DC (27 June 2024)
EU RoHS	Compliant per EU 2015/863

[Multiple Part Product Compliance Statements](#)
- Eu RoHS
- REACH SVHC
- Low-Halogen

[Multiple Part Industry Compliance Documents](#)

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Connector Housings
Series	33472
Description	MX150 Mat-Sealed Female Connector Assembly, Dual Row, 20 Circuits, Keying Option B, with Clipslot, without Connector Position Assurance, Light Gray
Application	Power, Wire-to-Board, Wire-to-Wire, Automotive
Product Family	MX150 Sealed and Unsealed Connector System
Product Name	MX150
UPC	191128449120

Agency

UL	E29179
----	--------

Physical

Circuits (maximum)	20
Color - Resin	Gray (Light)
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	SPS/Nylon
Net Weight	22.100/g
Number of Rows	2
Packaging Type	Partitioned Carton

Panel Mount	No
Pitch - Mating Interface	3.50mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +150°C

Mates With / Use With

Mates with Part(s)

Description	Part Number
MX150 Mat-Sealed Dual Row Male Connector Assemblies	<u>33482</u>

Use with Part(s)

Description	Part Number
MX150 Sealed Receptacle Cavity Plug	<u>343454001</u>
MX150 90° Backshell Adapter for Female Sealed Connector Assembly, 16 or 20 Circuit, with Rib	<u>349511631</u>
MX150 90° Backshell Adapter for Female Sealed Connector Assembly, 16 or 20 Circuit, without Rib	<u>349511641</u>
MX150 Backshell for Female Sealed Connector Assembly, 20 Circuit, without Rib	<u>349512021</u>
MX150 Female Terminals	<u>33001</u>
MX150 Female Terminals	<u>33012</u>