



Main

Product Range	Harmony Electromechanical Relays
Product Type	Socket
Product Compatibility	Relay 792XDX Relay 782XDXH
Number of Terminals	14
Switch Function	4PDT
Contact Composition	4 C/O

Complementary

Rated Current	5 A
[Ue] rated operational voltage	120 V
Contact Terminal Arrangement	Mixed
Connections Terminals	Pins for printed circuit board
Fixing Mode	By screws printed circuit boards
Product Weight	0.2 oz (5.8 g)
Width	0.7 in (16.6 mm)
Depth	1.0000000000 in (25.40 mm)

Environment

Ambient Air Temperature for Storage	-40...221 °F (-40...105 °C)
Ambient Air Temperature for Operation	-40...131 °F (-40...55 °C)
Flame Retardance	UL94-V0
Product Certifications	UL[RETURN]CSA[RETURN]CE

Ordering and shipping details

Category	US10CP221127
Discount Schedule	0CP2
GTIN	3606480277900
Returnability	No
Country of origin	CN

Packing Units


Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.700 in (1.778 cm)
Package 1 Width	0.800 in (2.032 cm)
Package 1 Length	1.100 in (2.794 cm)
Package 1 Weight	0.160 oz (4.536 g)
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	0.9 in (2.2 cm)

Package 2 Width	1.1 in (2.8 cm)
Package 2 Length	5.2 in (13.2 cm)
Package 2 Weight	2.05 oz (58 g)
Unit Type of Package 3	CAR
Number of Units in Package 3	1000
Package 3 Height	8.3 in (21 cm)
Package 3 Width	11.4 in (29 cm)
Package 3 Length	13.0 in (33 cm)
Package 3 Weight	13.007 lb(US) (5.9 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	"WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov "
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Wiring Diagram



- (1) : N.C.
- (2) : N.O.
- (3) : COM
- (4) : Input
- (5) : Ground lug