

VS-08-SET-MOD-1-R/5-BU-BU/SD-F - Panel-mount frame



1658833

<https://www.phoenixcontact.com/us/products/1658833>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



RJ45 panel mounting frame, IP67, for round panel cutout, with grommet, with thread and union nut, with RJ45 socket insert, CAT5e, socket on socket, with protective cover, flat design

Commercial data

Item number	1658833
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB17
Product key	ABNNDB
GTIN	4046356164436
Weight per piece (including packing)	24.8 g
Weight per piece (excluding packing)	20.9 g
Customs tariff number	85369010
Country of origin	DE

1658833
<https://www.phoenixcontact.com/us/products/1658833>

Technical data

Product properties

Product type	Panel-mount frame
Type	Version 6
Connection profile	RJ45
Type	RJ45

Data management status

Article revision	05
------------------	----

Electrical properties

Transmission medium	Copper
---------------------	--------

Material specifications

Material	Plastic
Housing material	Plastic

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP67
----------------------	------

Mounting

Mounting type	Front mounting
Thread type	()

VS-08-SET-MOD-1-R/5-BU-BU/SD-F - Panel-mount frame




1658833

<https://www.phoenixcontact.com/us/products/1658833>

Drawings

Dimensional drawing



Protective cover, IP67


VS-08-SET-MOD-1-R/5-BU-BU/SD-F - Panel-mount frame



1658833

<https://www.phoenixcontact.com/us/products/1658833>

Dimensional drawing



Mounting cutout


VS-08-SET-MOD-1-R/5-BU-BU/SD-F - Panel-mount frame



1658833

<https://www.phoenixcontact.com/us/products/1658833>

Dimensional drawing



RJ45 panel mounting frame, IP67

VS-08-SET-MOD-1-R/5-BU-BU/SD-F - Panel-mount frame



1658833
<https://www.phoenixcontact.com/us/products/1658833>

Classifications

ECLASS

ECLASS-11.0	27440210
ECLASS-12.0	27440210
ECLASS-13.0	27440210

ETIM

ETIM 9.0	EC002310
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

1658833
<https://www.phoenixcontact.com/us/products/1658833>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2024 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com