



General ordering data

| | |
|------------------|--|
| Order No. | 1840990000 |
| Part designation | SL-SMT5.00/9/180 3.2SN SW BOX |
| Version | PCB plug-in connector, Male connectors, Reflow solder connection, Pitch: 5.00 mm, No. of poles: 9, 180°, Box |
| EAN | 4032248351886 |
| Qty. | 50 pc(s). |

System parameters

| | |
|-----------------------------|--------------------------|
| Fitted to PCB | Reflow solder connection |
| Outgoing elbow | 180° |
| Pitch | 5 mm |
| Pitch in inch | 0.197 inch |
| No. of poles | 9 |
| Solder pin length | 3.2 mm |
| Can be coded | Yes |
| No. of rows | 1 |
| No. of solder pins per pole | 1 |
| Fitting hole tolerance | + 0.1 mm |
| L1 in mm | 40 mm |
| L1 in inch | 1.575 inch |
| Insulation resistance | 1 MΩ |

Material data

| | |
|---------------------------------------|---------------------|
| Insulating material | LCP GF |
| Colour | black |
| colour chart | Similar to RAL 9011 |
| Insulating material group | IIIa |
| Flammability class UL 94 | V-0 |
| CTI | >= 175 |
| Contact base material | CuSn |
| Contact surface | tinned |
| Constant operating temp., min. | -25 °C |
| Constant operating temp., max. | 100 |
| Storage temperature, min. | -25 °C |
| Storage temperature, max. | 55 °C |
| Max. relative humidity during storage | 80 % |

DIN IEC rating data

| | |
|--|-------|
| Rated current, min. No. pins (Tu=20°C) | 19 A |
| Rated current, max. No. pins (Tu=20°C) | 15 A |
| Rated current, min. No. pins(Tu=40°C) | 16 A |
| Rated current, max. No. pins (Tu=40°C) | 13 A |
| Rated voltage for overvoltage class/pollution severity III/3 | 250 V |
| Rated impulse withstand voltage for overvoltage class/pollution severity III/3 | 4 kV |
| Rated voltage for overvoltage class/pollution severity III/2 | 320 V |
| Rated impulse withstand voltage for overvoltage class/pollution severity III/2 | 4 kV |
| Rated voltage for overvoltage class/pollution severity II/2 | 400 V |
| Rated impulse withstand voltage for overvoltage class/pollution severity II/2 | 4 kV |

CSA rating data

| | |
|-----------------------------|-------|
| Rated voltage (Use group D) | 300 V |
| Rated current (Use group D) | 10 A |

UL 1059 rating data

| | |
|-----------------------------|-------|
| Rated voltage (Use group D) | 300 V |
| Rated current (Use group D) | 10 A |

Approvals

Approvals institutes



Classifications

| | |
|------------|-------------|
| ETIM 2.0 | NK |
| ETIM 3.0 | EC001284 |
| eClass 4.1 | 27-26-07-01 |
| eClass 5.0 | 27-26-07-01 |
| eClass 5.1 | 27-26-07-04 |

Similar products

| Order No. | Part designation | Version |
|------------|-------------------------------|--|
| 1796480000 | SL-SMT5.00/2/180 1.5SN | PCB plug-in connector, Male connectors, Reflow solder connection, Pitch: 5.00 mm, No. of poles: 2, 180°, Box |
| 1840920000 | SL-SMT5.00/2/180 3.2SN SW BOX | PCB plug-in connector, Male connectors, Reflow solder connection, Pitch: 5.00 mm, No. of poles: 2, 180°, Box |
| 1796490000 | SL-SMT5.00/3/180 1.5SN | PCB plug-in connector, Male connectors, Reflow solder connection, Pitch: 5.00 mm, No. of poles: 3, 180°, Box |
| 1840930000 | SL-SMT5.00/3/180 3.2SN SW BOX | PCB plug-in connector, Male connectors, Reflow solder connection, Pitch: 5.00 mm, No. of poles: 3, 180°, Box |
| 1796500000 | SL-SMT5.00/4/180 1.5SN | PCB plug-in connector, Male connectors, Reflow solder connection, Pitch: 5.00 mm, No. of poles: 4, 180°, Box |
| 1840940000 | SL-SMT5.00/4/180 3.2SN SW BOX | PCB plug-in connector, Male connectors, Reflow solder connection, Pitch: 5.00 mm, No. of poles: 4, 180°, Box |
| 1796510000 | SL-SMT5.00/5/180 1.5SN | PCB plug-in connector, Male connectors, Reflow solder connection, Pitch: 5.00 mm, No. of poles: 5, 180°, Box |
| 1840950000 | SL-SMT5.00/5/180 3.2SN SW BOX | PCB plug-in connector, Male connectors, Reflow solder connection, Pitch: 5.00 mm, No. of poles: 5, 180°, Box |
| 1796520000 | SL-SMT5.00/6/180 1.5SN | PCB plug-in connector, Male connectors, Reflow solder connection, Pitch: 5.00 mm, No. of poles: 6, 180°, Box |
| 1840960000 | SL-SMT5.00/6/180 3.2SN SW BOX | PCB plug-in connector, Male connectors, Reflow solder connection, Pitch: 5.00 mm, No. of poles: 6, 180°, Box |
| 1796530000 | SL-SMT5.00/7/180 1.5SN | PCB plug-in connector, Male connectors, Reflow solder connection, Pitch: 5.00 mm, No. of poles: 7, 180°, Box |
| 1840970000 | SL-SMT5.00/7/180 3.2SN SW BOX | PCB plug-in connector, Male connectors, Reflow solder connection, Pitch: 5.00 mm, No. of poles: 7, 180°, Box |

| | | |
|------------|--------------------------------|---|
| 1796540000 | SL-SMT5.00/8/180 1.5SN | PCB plug-in connector, Male connectors, Reflow solder connection, Pitch: 5.00 mm, No. of poles: 8, 180°, Box |
| 1840980000 | SL-SMT5.00/8/180 3.2SN SW BOX | PCB plug-in connector, Male connectors, Reflow solder connection, Pitch: 5.00 mm, No. of poles: 8, 180°, Box |
| 1796550000 | SL-SMT5.00/9/180 1.5SN | PCB plug-in connector, Male connectors, Reflow solder connection, Pitch: 5.00 mm, No. of poles: 9, 180°, Box |
| 1796560000 | SL-SMT5.00/10/180 1.5SN | PCB plug-in connector, Male connectors, Reflow solder connection, Pitch: 5.00 mm, No. of poles: 10, 180°, Box |
| 1841000000 | SL-SMT5.00/10/180 3.2SN SW BOX | PCB plug-in connector, Male connectors, Reflow solder connection, Pitch: 5.00 mm, No. of poles: 10, 180°, Box |
| 1796570000 | SL-SMT5.00/11/180 1.5SN | PCB plug-in connector, Male connectors, Reflow solder connection, Pitch: 5.00 mm, No. of poles: 11, 180°, Box |
| 1841020000 | SL-SMT5.00/11/180 3.2SN SW BOX | PCB plug-in connector, Male connectors, Reflow solder connection, Pitch: 5.00 mm, No. of poles: 11, 180°, Box |
| 1796580000 | SL-SMT5.00/12/180 1.5SN | PCB plug-in connector, Male connectors, Reflow solder connection, Pitch: 5.00 mm, No. of poles: 12, 180°, Box |
| 1841030000 | SL-SMT5.00/12/180 3.2SN SW BOX | PCB plug-in connector, Male connectors, Reflow solder connection, Pitch: 5.00 mm, No. of poles: 12, 180°, Box |
| 1796590000 | SL-SMT5.00/13/180 1.5SN | PCB plug-in connector, Male connectors, Reflow solder connection, Pitch: 5.00 mm, No. of poles: 13, 180°, Box |
| 1841040000 | SL-SMT5.00/13/180 3.2SN SW BOX | PCB plug-in connector, Male connectors, Reflow solder connection, Pitch: 5.00 mm, No. of poles: 13, 180°, Box |
| 1796600000 | SL-SMT5.00/14/180 1.5SN | PCB plug-in connector, Male connectors, Reflow solder connection, Pitch: 5.00 mm, No. of poles: 14, 180°, Box |
| 1841050000 | SL-SMT5.00/14/180 3.2SN SW BOX | PCB plug-in connector, Male connectors, Reflow solder connection, Pitch: 5.00 mm, No. of poles: 14, 180°, Box |
| 1796610000 | SL-SMT5.00/15/180 1.5SN | PCB plug-in connector, Male connectors, Reflow solder connection, Pitch: 5.00 mm, No. of poles: 15, 180°, Box |
| 1841060000 | SL-SMT5.00/15/180 3.2SN SW BOX | PCB plug-in connector, Male connectors, Reflow solder connection, Pitch: 5.00 mm, No. of poles: 15, 180°, Box |
| 1796620000 | SL-SMT5.00/16/180 1.5SN | PCB plug-in connector, Male connectors, Reflow solder connection, Pitch: 5.00 mm, No. of poles: 16, 180°, Box |
| 1841070000 | SL-SMT5.00/16/180 3.2SN SW BOX | PCB plug-in connector, Male connectors, Reflow solder connection, Pitch: 5.00 mm, No. of poles: 16, 180°, Box |
| 1841080000 | SL-SMT5.00/17/180 3.2SN SW BOX | PCB plug-in connector, Male connectors, Reflow solder connection, Pitch: 5.00 mm, No. of poles: 17, 180°, Box |
| 1841090000 | SL-SMT5.00/18/180 3.2SN SW BOX | PCB plug-in connector, Male connectors, Reflow solder connection, Pitch: 5.00 mm, No. of poles: 18, 180°, Box |
| 1841100000 | SL-SMT5.00/19/180 3.2SN SW BOX | PCB plug-in connector, Male connectors, Reflow solder connection, Pitch: 5.00 mm, No. of poles: 19, 180°, Box |
| 1841110000 | SL-SMT5.00/20/180 3.2SN SW BOX | PCB plug-in connector, Male connectors, Reflow solder connection, Pitch: 5.00 mm, No. of poles: 20, 180°, Box |
| 1841120000 | SL-SMT5.00/21/180 3.2SN SW BOX | PCB plug-in connector, Male connectors, Reflow solder connection, Pitch: 5.00 mm, No. of poles: 21, 180°, Box |
| 1841130000 | SL-SMT5.00/22/180 3.2SN SW BOX | PCB plug-in connector, Male connectors, Reflow solder connection, Pitch: 5.00 mm, No. of poles: 22, 180°, Box |
| 1841140000 | SL-SMT5.00/23/180 3.2SN SW BOX | PCB plug-in connector, Male connectors, Reflow solder connection, Pitch: 5.00 mm, No. of poles: 23, 180°, Box |
| 1841150000 | SL-SMT5.00/24/180 3.2SN SW BOX | PCB plug-in connector, Male connectors, Reflow solder connection, Pitch: 5.00 mm, No. of poles: 24, 180°, Box |