

## Cat6/Cat5e 110 Style Punch Down Keystone Jack - Green, TAA

MODEL NUMBER: N238-001-GN



### Highlights

- Use in Cat6 or Cat5e installations
- Compliant with EIA/TIA CAT6 connecting hardware specifications.
- Dual-color coded labeling made for both 568A and 568B (258A) wiring schemes.
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

### Package Includes

- Green Cat6/Cat5e 110 Punch Down Keystone Jack
- Termination caps (2)

### Description

These Cat6/Cat5e 110-Style Punch-Down Keystone Jacks provide maximum flexibility for any UTP Ethernet environment. Ideal for Cat5e cabling environments, the jack also meets UL-certified ANSI/TIA/EIA-568-B.2-1 Permanent Link/Channel Identification Test for Cat6 cabling installations. The uniquely patterned printed circuit board construction is designed to meet Cat6 250 MHz performance, and is fully compliant with EIA/TIA CAT6 connecting hardware specifications. With its compact casing, it fits into any conventional face plate, outlet box or panel. It also features dual-color-coded labeling made for both 568A and 568B (258A) wiring schemes.  
UTP Cat6 22-24 AWG solid cable

### Features

- Use in Cat6 or Cat5e installations
- Compliant with EIA/TIA Cat6 connecting hardware specifications
- Dual-color coded labeling made for both 568A & 568B (258A) wiring schemes
- Compact casing fits into any conventional face plate, outlet box, or panel
- UL-certified ANSI/TIA/EIA-568-B.2-1 Permanent Link/Channel Identification Test
- Uniquely patterned, printed circuit board designed to meet Cat6 performances
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

## Specifications

| OVERVIEW     |                    |
|--------------|--------------------|
| UPC Code     | 037332153562       |
| Product Type | RJ45 Keystone Jack |
| Technology   | Cat5/5e; Cat6      |
| CONNECTIONS  |                    |



Powering Business Worldwide

TRIPP LITE  
SERIES

|                                     |                            |
|-------------------------------------|----------------------------|
| Number of Ports                     | 1                          |
| Side A - Connector 1                | RJ45 (FEMALE)              |
| Side B - Connector 1                | 110 IDC                    |
| <b>PHYSICAL</b>                     |                            |
| Color                               | Green                      |
| Connector Color                     | Green                      |
| Shipping Dimensions (hwd / in.)     | 0.25 x 0.50 x 0.50         |
| Shipping Dimensions (hwd / cm)      | 0.64 x 1.27 x 1.27         |
| Shipping Weight (lbs.)              | 0.05                       |
| Shipping Weight (kg)                | 0.02                       |
| Unit Dimensions (hwd / in.)         | 0.000 x 0.000 x 0.000      |
| <b>STANDARDS &amp; COMPLIANCE</b>   |                            |
| Product Compliance                  | Trade Agreements Act (TAA) |
| <b>WARRANTY &amp; SUPPORT</b>       |                            |
| Product Warranty Period (Worldwide) | Lifetime limited warranty  |

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.