

# KP DCS 4,8-6,4 K6 C4 P7 - Membrane keypad



2203572

<https://www.phoenixcontact.com/us/products/2203572>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Membrane keypad, self-adhesive, silver conduction technology, 6 keys, embossed, 4 colors, connecting cable: 50 mm, pitch: 1.0 mm, operating temperature: -20°C ... 70°C

## Your advantages

- Customer-specific key layouts on request
- Easy integration into DCS series electronics housings

## Commercial data

Item number	2203572
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AC02
Product key	ACFBAF
GTIN	4055626472478
Weight per piece (including packing)	5.6 g
Weight per piece (excluding packing)	5.6 g
Customs tariff number	85365011
Country of origin	DE

# KP DCS 4,8-6,4 K6 C4 P7 - Membrane keypad



2203572

<https://www.phoenixcontact.com/us/products/2203572>

## Technical data

### Product properties

Product type	Membrane keypad
Housing type	Display carrier
Housing series	DCS
Number of positions	7
Pitch	1 mm
Technology	Conductive silver/graphite (T6/4 Cu/Ag)
Embossing	Dome embossing 11 x 11 mm
Number of socket pins	7
Number of keys	6 (1 x 6)

### Data management status

Article revision	01
------------------	----

### Dimensions

Length	50 mm (Membrane cable)
Pitch	1 mm
Dimensions	23 mm x 103 mm

### Material specifications

Housing material	Polyester
------------------	-----------

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-20 °C ... 70 °C
Ambient temperature (storage/transport)	-40 °C ... 80 °C

### Mounting

Mounting type	adhesive
---------------	----------

# KP DCS 4,8-6,4 K6 C4 P7 - Membrane keypad



2203572

<https://www.phoenixcontact.com/us/products/2203572>

## Classifications

### ECLASS

ECLASS-11.0	27182702
ECLASS-13.0	27190605

### ETIM

ETIM 9.0	EC002779
----------	----------

### UNSPSC

UNSPSC 21.0	31261500
-------------	----------

# KP DCS 4,8-6,4 K6 C4 P7 - Membrane keypad



2203572

<https://www.phoenixcontact.com/us/products/2203572>

## Accessories

### DCS 5,7 M 1F RL W C 7035 - Electronics housing

2203174

<https://www.phoenixcontact.com/us/products/2203174>



Display housing, 5.7", light gray, consisting of two half shells with screws, window in the middle. Front 1.1 mm recessed, keypad areas on the left and right recessed for wall installation

---

### DCS 5,7 L 1F R BP 1 7035 - Electronics housing

2203175

<https://www.phoenixcontact.com/us/products/2203175>



Display housing, 5.7", light gray, consisting of two half shells, four front plates with screws and battery pack contacts, window on the left. Front 1.1 mm recessed, keypad area on the right, recessed for battery pack

# KP DCS 4,8-6,4 K6 C4 P7 - Membrane keypad



2203572

<https://www.phoenixcontact.com/us/products/2203572>

## DCS 5,7 L 1F R W C 7035 - Electronics housing

2203176

<https://www.phoenixcontact.com/us/products/2203176>



Display housing, 5.7", light gray, consisting of two half shells with screws, window on the left. Front 1.1 mm recessed, keypad area on the right recessed for wall installation

---

Phoenix Contact 2024 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)