

1593679
<https://www.phoenixcontact.com/us/products/1593679>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



M23, Device connector front mounting, series: RC, straight, shielded: yes, Screw locking mechanism, No. of pos.: 6, Direction of rotation: Standard, contact connection type: Socket, Solder cup, Flat gasket, 4x Ø 3.2, coding: N, Alternative product in accordance with RoHS II without Exemption 6c (Pb < 0.1 %) item no.: 1240401

Commercial data

Item number	1593679
Packing unit	40 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	AB31
Product key	ABRAFL
GTIN	4046356197489
Weight per piece (including packing)	31.1 g
Weight per piece (excluding packing)	31.1 g
Customs tariff number	85366990
Country of origin	DE

RC-06S1N122300 - Device connector front mounting



1593679

<https://www.phoenixcontact.com/us/products/1593679>

Technical data

Product properties

Product type	Circular connectors (device side)
--------------	-----------------------------------


Connector

Insulating body	
Coding	N
Insertion/withdrawal cycles	50
Connection method	Solder cup
Contact switching type	Socket
Application	Signal
Number of positions	6
Direction of rotation	Standard
Connection profile	6
Contact diameter	2 mm
Power contacts	
Litz wire cross-section Power contacts min.	0.08 mm²
Litz wire cross-section Power contacts max.	2.5 mm²
Rated current Power contacts	20 A
Rated voltage	48 V AC
	74 V DC
Rated surge voltage	1.5 kV
Overvoltage category	III
Degree of pollution	3

Housing	
Housing material	Metal
Type of locking	Screw locking mechanism
Pg screw connection	none
Degree of protection (plugged in)	IP67
Thread type	M23

Drawings

Schematic diagram



Connector pin assignment


RC-06S1N122300 - Device connector front mounting

1593679

<https://www.phoenixcontact.com/us/products/1593679>



Dimensional drawing



Installation dimensions

RC-06S1N122300 - Device connector front mounting



1593679

<https://www.phoenixcontact.com/us/products/1593679>

Classifications

ECLASS

ECLASS-11.0	27440102
ECLASS-12.0	27440116
ECLASS-13.0	27440116

ETIM

ETIM 9.0	EC002635
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	41bd9e4e-a74a-4520-96df-58b9bc594ff2