

**General ordering data**

Order No.	7906080000
Part designation	BK 4/E
Version	Single- and multi-pole terminal strip, 4 mm <sup>2</sup> , Screw connection, KrG, Medium yellow, Direct mounting
EAN	4008190576288
Qty.	100 pc(s).

**Product notes**

Note, technical data	2 single-wire conductors with same cross-section (0.5...1.5 mm <sup>2</sup> ) can be connected.
----------------------	---

**PT OKIECEx/ATEX rating data**

EU-type examination certificate	SIRA01ATEX3247U
Download English	SIRA01ATEX3247U_e.pdf
IECEx Certificate of Conformity	IECEXSIR05.0035U
Download	IECEXSIR05.0035U_e.pdf
ATEX voltage	275 V
ATEX current	28 A
ATEX conductor cross-section	4 mm <sup>2</sup>
IECEx voltage	275 V
IECEx current	28 A
IECEx conductor cross-section	4 mm <sup>2</sup>
Voltage when using cross-connections	CrossConnectionGuide.pdf
Operating temperature range	Einsatztemperaturbereich siehe EG-Baumusterprüfungsbescheinigung/IECEx-Certificate of Conformity
Marking EN 60079-7	Ex e II

**Approvals**

Approvals institutes

**Classifications**

ETIM 2.0	EC001284
ETIM 3.0	EC001284
eClass 4.1	27-14-11-06
eClass 5.0	27-14-11-06
eClass 5.1	27-14-11-06

**Similar products**

Order No.	Part designation	Version
0624720000	BK 2 CRN	Single- and multi-pole terminal strip, 4 mm <sup>2</sup> , Screw connection, KrG, Medium yellow, Direct mounting
0624920000	BK 3 CRN	Single- and multi-pole terminal strip, 4 mm <sup>2</sup> , Screw connection, KrG, Medium yellow, Direct mounting

0625120000	BK 4 CRN	Single- and multi-pole terminal strip, 4 mm <sup>2</sup> , Screw connection, KrG, Medium yellow, Direct mounting
0625220000	BK 6 CRN	Single- and multi-pole terminal strip, 4 mm <sup>2</sup> , Screw connection, KrG, Medium yellow, Direct mounting
0625320000	BK 12 CRN	Single- and multi-pole terminal strip, 4 mm <sup>2</sup> , Screw connection, KrG, Medium yellow, Direct mounting
7906040000	BK 2/E	Single- and multi-pole terminal strip, 4 mm <sup>2</sup> , Screw connection, KrG, Medium yellow, Direct mounting
7906060000	BK 3/E	Single- and multi-pole terminal strip, 4 mm <sup>2</sup> , Screw connection, KrG, Medium yellow, Direct mounting
7906090000	BK 6/E	Single- and multi-pole terminal strip, 4 mm <sup>2</sup> , Screw connection, KrG, Medium yellow, Direct mounting
7906100000	BK 12/E	Single- and multi-pole terminal strip, 4 mm <sup>2</sup> , Screw connection, KrG, Medium yellow, Direct mounting