

## PD10AA47 Product Details

**PD10AA47**  
(1618256-6)

TE Internal Number: 1618256-6

**High Voltage Relays**[Not EU RoHS or ELV Compliant](#)**Product Highlights:**

- Contact Arrangement = 1 Form A, SPST-NO, 1 N/O
- Power Switching = Make Only, Yes, No
- Contact Current Rating = 0 - 10 Amps.
- Not RF Rated
- Coil Voltage = 12 VDC

[View all Features](#)**Quick Links**[Check Pricing & Availability](#)[Search for Tooling](#)[Product Feature Selector](#)[Contact Us About This Product](#) [Add to My Part List](#) [Request Sample](#) [Find Similar Products](#) [Buy Product](#)**Documentation & Additional Information****Product Drawings:**

- None Available

**Catalog Pages/Data Sheets:**

- None Available

**Product Specifications:**

- None Available

**Application Specifications:**

- None Available

**Instruction Sheets:**

- None Available

**CAD Files:**

- None Available

**Additional Information:**

- [Product Line Information](#)

**Related Products:**

- [Tooling](#)

**Product Features** (Please use the Product Drawing for all design activity)**Product Type Features:**

- [Termination Style](#) = Stud Terminal

**Electrical Characteristics:**

- [Contact Current Rating \(Amps.\)](#) = 0 - 10
- [RF Rated](#) = No
- [Coil Voltage \(VDC\)](#) = 12
- [Voltage, Max. \(VDC\)](#) = 0 - 1800
- Current, Carry Only = Yes

**Termination Related Features:**

- [High Voltage Connection \(Power\)](#) = PCB Solder Connection
- [High Voltage Connection \(Coil\)](#) = Stud Terminal
- [Auxiliary Contacts](#) = Without

**Body Related Features:**

- [Mount Style](#) = Panel

**Configuration Related Features:**

- [Contact Arrangement](#) = 1 Form A, SPST-NO, 1 N/O
- [Power Switching](#) = Make Only, Yes, No
- [Economizer](#) = Without

**Industry Standards:**

- [RoHS/ELV Compliance](#) = Not ELV/RoHS compliant
- [Lead Free Solder Processes](#) = Not suitable for lead free processing

**Other:**

- Brand = Kilovac

**Corporate Information**[Who We Are](#)[Investors](#)[News Room](#)[Supplier Portal](#)[Careers](#)**Quick Links**[Check Distributor Inventory](#)[Cross Reference](#)[Find Documents & Drawings](#)[Product Compliance Support Center](#)[Site Map](#)**Customer Support**[Email or Chat with Us](#)[Find a Phone Number](#)[Search Knowledge Base](#)[Manage Your Account](#)