



Have a Question?

Chat with a Product
Information Specialist



What can we help you find?



[Products](#) | [Industries](#) | [Resources](#) | [About TE](#) | [My Account](#) | [Innovation](#) | [Support Center](#)


[Home](#) > [Products](#) > [Switches & Knobs](#) > [Product Feature Selector](#) > Product Details

1520136-2 Product Details

[Share](#)

[Print](#)

[Email](#)



1520136-2

TE Internal Number: 1520136-2

Active

Power Toggle Switches



Always EU RoHS/ELV Compliant ([Statement of Compliance](#))

Product Highlights:

- Double Pole - Single Throw Configuration (Pole-Throw)
- Toggle Length = 12.70 mm
- Toggle Style = Baton with Ball
- Bushing Length = 11.50 mm
- Termination Type = Screw-In Terminal

[View all Features](#)

Quick Links

- ▶ [Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)



[Add to My Part List](#)



[Request Sample](#)



[Find Similar Products](#)



[Buy Product](#)

Documentation & Additional Information

Product Drawings:

- None Available

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Related Products:

- [Tooling](#)

[Feedback](#)

Product Features (Please use the Product Drawing for all design activity)

Electrical Characteristics:

- UL/CSA 125V Current Rating (A) = 20
- UL/CSA 250V Current Rating (A) = 10
- UL/CSA 125V Horse Power Rating (hp) = 1.50
- UL/CSA 250V Horse Power Rating (hp) = 1.50

Termination Features:

- Termination Type = Screw-In Terminal

Dimensions:

- Toggle Length (mm [in]) = 12.70 [0.500]
- Bushing Length (mm [in]) = 11.50 [0.453]

Housing Features:

- Toggle Style = Baton with Ball

Configuration Features:

- Configuration (Pole-Throw) = Double Pole - Single Throw

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not reviewed for lead free solder process
- RoHS/ELV Compliance History = Always was RoHS compliant

Other:

- Brand = Alcoswitch

Corporate Information

[About TE](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)
[Careers](#)
[Terms & Conditions](#)
[Privacy Policy](#)
[AODA Accessibility Policy](#)
[AODA Multi-Year Accessibility Plan](#)

Quick Links

[Distributor Inventory](#)
[Product Cross Reference](#)
[Documents & Drawings](#)
[Product Compliance Support Center](#)
[Site Map](#)

Customer Support

[Email or Chat With Us](#)
[Find a Phone Number](#)
[Knowledge Base](#)
[Manage Your Account](#)

Keep Me Informed



