

PD90XA57 Product Details



PD90XA57
(7-1618013-2)

TE Internal Number: 7-1618013-2

Active

High Voltage Relays

[Not EU RoHS or ELV Compliant](#)

Product Highlights:

- Contact Arrangement = 1 Form A, SPST-NO, 1 N/O
- Power Switching = Make Only, Yes, No
- Contact Current Rating = 0 - 90 Amps.
- Not RF Rated
- Coil Voltage = 12 VDC

[View all Features](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

[Add to My Part List](#) [Request Sample](#) [Find Similar Products](#) [Buy Product](#)

Documentation & Additional Information

Product Drawings:

- None Available

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Termination Style](#) = Stud Terminal

Electrical Characteristics:

- [Contact Current Rating \(Amps.\)](#) = 0 - 90
- [RF Rated](#) = No
- [Coil Voltage \(VDC\)](#) = 12
- [Voltage, Max. \(VDC\)](#) = 0 - 1800
- [Current, Carry Only](#) = Yes

Termination Related Features:

- [High Voltage Connection \(Power\)](#) = Stud Terminal
- [High Voltage Connection \(Coil\)](#) = Stud Terminal
- [Auxiliary Contacts](#) = Without

Body Related Features:

- [Mount Style](#) = Panel

Configuration Related Features:

- [Contact Arrangement](#) = 1 Form A, SPST-NO, 1 N/O
- [Power Switching](#) = Make Only, Yes, No
- [Economizer](#) = Without

Industry Standards:

- [RoHS/ELV Compliance](#) = Not ELV/RoHS compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process

Other:

- Brand = Kilovac

Corporate Information

- [Who We Are](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)

Quick Links

- [Check Distributor Inventory](#)
- [Cross Reference](#)
- [Find Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

Customer Support

- [Email or Chat with Us](#)
- [Find a Phone Number](#)
- [Search Knowledge Base](#)
- [Manage Your Account](#)