

Accessories
E 18/50A WS**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

**Klippon® Connect with clamping yoke Technology**

The high reliability and variety of designs of the terminal blocks with clamping yoke connections make planning easier and optimises operational safety. Klippon® Connect provides a proven response to a range of different requirements.

General ordering data

Type	E 18/50A WS
Order No.	0361600000
Version	Active components, Cartridge fuse
GTIN (EAN)	4008190144173
Qty.	10 pc(s).

Accessories

E 18/50A WS

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Dimensions and weights

Net weight	13.8 g
------------	--------

Temperatures

Operating temperature	Storage temperature
-----------------------	---------------------

Material data

Colour	Beige
--------	-------

System specifications

Version	Fuse accessories
---------	------------------

Fuse cartridges

Characteristics	slo-blo	Colour	Beige
Version	Fuse accessories		

Rating data

Rated voltage	380 V	Rated current	50 A
---------------	-------	---------------	------

Classifications

ETIM 3.0	EC000099	ETIM 4.0	EC000099
ETIM 5.0	EC000099	ETIM 6.0	EC000099
UNSPSC	30-21-18-12	eClass 5.1	27-14-20-04
eClass 6.2	27-14-20-04	eClass 7.1	27-14-20-04
eClass 8.1	27-14-20-04	eClass 9.0	27-14-20-04
eClass 9.1	27-14-20-04		

Product information

Descriptive text ordering data	(M) = medium time-lag; (F) = quick-acting
Descriptive text technical data	1) The company SIBA supplies G-type fuse cartridges 5 x 25 with indicator, also in marine engineering version for 450 V~. 2) Fuse cartridges 5 x 30 (500 V~) für SAKS 3 are available from the company WICKMANN. 3) The company LINDNER supplies Neozed fuse cartridges, also in a further marine engineering version for 440 V~. 4) Fuse cartridges with the dimensions 1"x1/4" = 25.4x6.35 mm and 13/32"x11/2" = 10.3x38.1 mm are not in the programme. 5) Only for SAKS 1 and SAKS 7.

Approvals

ROHS	Conform
------	---------

Downloads

Brochure/Catalogue	CAT 1 TERM 16/17 EN
Engineering Data	WSCAD