



General ordering data

| | |
|------------------|---|
| Order No. | 1841700000 |
| Part designation | SL-SMT3.5/9/90G 3.2SN SW BOX |
| Version | PCB plug-in connector, Male connectors, Reflow solder connection, Pitch: 3.50 mm, No. of poles: 9, 90°, Box |
| EAN | 4032248353057 |
| Qty. | 50 pc(s). |

System parameters

| | |
|-----------------------------|--------------------------|
| Fitted to PCB | Reflow solder connection |
| Outgoing elbow | 90° |
| Pitch | 3.5 mm |
| Pitch in inch | 0.138 inch |
| No. of poles | 9 |
| Solder pin length | 3.2 mm |
| Can be coded | Yes |
| No. of rows | 1 |
| No. of solder pins per pole | 1 |
| Dia. of fitting hole | 1.4 mm |
| Fitting hole tolerance | + 0.1 mm |
| L1 in mm | 28 mm |
| L1 in inch | 1.102 inch |
| Insulation resistance | 1 MΩ |

System parameters

| | |
|---|------------------------------|
| Electric shock protection to DIN VDE 0470 | IP 10 |
| Electric shock protection to DIN VDE 0470 | Safe from back-of-hand touch |

Material data

| | |
|---------------------------------------|---------------------|
| Insulating material | LCP GF |
| Colour | black |
| colour chart | Similar to RAL 9011 |
| Insulating material group | IIIa |
| Flammability class UL 94 | V-0 |
| CTI | >= 175 |
| Temperature of glow-wire test | 960 °C |
| Duration of glow-wire test | 30 S |
| Contact base material | CuSn |
| Contact surface | tinned |
| Constant operating temp., min. | -25 °C |
| Constant operating temp., max. | 100 °C |
| Storage temperature, min. | -25 °C |
| Storage temperature, max. | 55 °C |
| Max. relative humidity during storage | 80 % |

DIN IEC rating data

| | |
|--|-------------------|
| Rated current, min. No. pins (Tu=20°C) | 15 A |
| Rated current, max. No. pins (Tu=20°C) | 12 A |
| Rated current, min. No. pins (Tu=40°C) | 13 A |
| Rated current, max. No. pins (Tu=40°C) | 10 A |
| Rated voltage for overvoltage class/pollution severity III/3 | 160 V |
| Rated impulse withstand voltage for overvoltage class/pollution severity III/3 | 2.5 kV |
| Rated voltage for overvoltage class/pollution severity III/2 | 160 V |
| Rated impulse withstand voltage for overvoltage class/pollution severity III/2 | 2.5 kV |
| Rated voltage for overvoltage class/pollution severity II/2 | 320 V |
| Rated impulse withstand voltage for overvoltage class/pollution severity II/2 | 2.5 kV |
| Short-time withstand current resistance | 3 x 1s with 100 A |

CSA rating data

| | |
|-----------------------------|-------|
| Rated voltage (Use group D) | 300 V |
| Rated current (Use group D) | 10 A |

UL 1059 rating data

| | |
|-----------------------------|-------|
| Rated voltage (Use group D) | 300 V |
| Rated current (Use group D) | 10 A |

Approvals

Approvals institutes



Downloads

CAD Library (P-CAD Format - Standard) SL-SMT.LIB

Classifications

| | |
|------------|-------------|
| ETIM 2.0 | NK |
| ETIM 3.0 | EC001284 |
| eClass 4.1 | 27-26-07-01 |
| eClass 5.0 | 27-26-07-01 |
| eClass 5.1 | 27-26-07-04 |

Similar products

| Order No. | Part designation | Version |
|------------|------------------------------|---|
| 1761552001 | SL-SMT3.5/3/90G 1.5SN | PCB plug-in connector, Male connectors, Reflow solder connection, Pitch: 3.50 mm, No. of poles: 3, 90°, Box |
| 1841640000 | SL-SMT3.5/3/90G 3.2SN SW BOX | PCB plug-in connector, Male connectors, Reflow solder connection, Pitch: 3.50 mm, No. of poles: 3, 90°, Box |
| 1761562001 | SL-SMT3.5/4/90G 1.5SN | PCB plug-in connector, Male connectors, Reflow solder connection, Pitch: 3.50 mm, No. of poles: 4, 90°, Box |
| 1841650000 | SL-SMT3.5/4/90G 3.2SN SW BOX | PCB plug-in connector, Male connectors, Reflow solder connection, Pitch: 3.50 mm, No. of poles: 4, 90°, Box |
| 1761572001 | SL-SMT3.5/5/90G 1.5SN | PCB plug-in connector, Male connectors, Reflow solder connection, Pitch: 3.50 mm, No. of poles: 5, 90°, Box |
| 1841660000 | SL-SMT3.5/5/90G 3.2SN SW BOX | PCB plug-in connector, Male connectors, Reflow solder connection, Pitch: 3.50 mm, No. of poles: 5, 90°, Box |
| 1761582001 | SL-SMT3.5/6/90G 1.5SN | PCB plug-in connector, Male connectors, Reflow solder connection, Pitch: 3.50 mm, No. of poles: 6, 90°, Box |
| 1841670000 | SL-SMT3.5/6/90G 3.2SN SW BOX | PCB plug-in connector, Male connectors, Reflow solder connection, Pitch: 3.50 mm, No. of poles: 6, 90°, Box |
| 1761592001 | SL-SMT3.5/7/90G 1.5SN | PCB plug-in connector, Male connectors, Reflow solder connection, Pitch: 3.50 mm, No. of poles: 7, 90°, Box |
| 1841680000 | SL-SMT3.5/7/90G 3.2SN SW BOX | PCB plug-in connector, Male connectors, Reflow solder connection, Pitch: 3.50 mm, No. of poles: 7, 90°, Box |

| | | |
|------------|-------------------------------|--|
| 1761602001 | SL-SMT3.5/8/90G 1.5SN | PCB plug-in connector, Male connectors, Reflow solder connection, Pitch: 3.50 mm, No. of poles: 8, 90°, Box |
| 1841690000 | SL-SMT3.5/8/90G 3.2SN SW BOX | PCB plug-in connector, Male connectors, Reflow solder connection, Pitch: 3.50 mm, No. of poles: 8, 90°, Box |
| 1761612001 | SL-SMT3.5/9/90G 1.5SN | PCB plug-in connector, Male connectors, Reflow solder connection, Pitch: 3.50 mm, No. of poles: 9, 90°, Box |
| 1761622001 | SL-SMT3.5/10/90G 1.5SN | PCB plug-in connector, Male connectors, Reflow solder connection, Pitch: 3.50 mm, No. of poles: 10, 90°, Box |
| 1841710000 | SL-SMT3.5/10/90G 3.2SN SW BOX | PCB plug-in connector, Male connectors, Reflow solder connection, Pitch: 3.50 mm, No. of poles: 10, 90°, Box |
| 1761632001 | SL-SMT3.5/11/90G 1.5SN | PCB plug-in connector, Male connectors, Reflow solder connection, Pitch: 3.50 mm, No. of poles: 11, 90°, Box |
| 1841720000 | SL-SMT3.5/11/90G 3.2SN SW BOX | PCB plug-in connector, Male connectors, Reflow solder connection, Pitch: 3.50 mm, No. of poles: 11, 90°, Box |
| 1761642001 | SL-SMT3.5/12/90G 1.5SN | PCB plug-in connector, Male connectors, Reflow solder connection, Pitch: 3.50 mm, No. of poles: 12, 90°, Box |
| 1841730000 | SL-SMT3.5/12/90G 3.2SN SW BOX | PCB plug-in connector, Male connectors, Reflow solder connection, Pitch: 3.50 mm, No. of poles: 12, 90°, Box |
| 1761652001 | SL-SMT3.5/13/90G 1.5SN | PCB plug-in connector, Male connectors, Reflow solder connection, Pitch: 3.50 mm, No. of poles: 13, 90°, Box |
| 1841740000 | SL-SMT3.5/13/90G 3.2SN SW BOX | PCB plug-in connector, Male connectors, Reflow solder connection, Pitch: 3.50 mm, No. of poles: 13, 90°, Box |
| 1761662001 | SL-SMT3.5/14/90G 1.5SN | PCB plug-in connector, Male connectors, Reflow solder connection, Pitch: 3.50 mm, No. of poles: 14, 90°, Box |
| 1841750000 | SL-SMT3.5/14/90G 3.2SN SW BOX | PCB plug-in connector, Male connectors, Reflow solder connection, Pitch: 3.50 mm, No. of poles: 14, 90°, Box |
| 1761672001 | SL-SMT3.5/15/90G 1.5SN | PCB plug-in connector, Male connectors, Reflow solder connection, Pitch: 3.50 mm, No. of poles: 15, 90°, Box |
| 1841760000 | SL-SMT3.5/15/90G 3.2SN SW BOX | PCB plug-in connector, Male connectors, Reflow solder connection, Pitch: 3.50 mm, No. of poles: 15, 90°, Box |
| 1761682001 | SL-SMT3.5/16/90G 1.5SN | PCB plug-in connector, Male connectors, Reflow solder connection, Pitch: 3.50 mm, No. of poles: 16, 90°, Box |
| 1841770000 | SL-SMT3.5/16/90G 3.2SN SW BOX | PCB plug-in connector, Male connectors, Reflow solder connection, Pitch: 3.50 mm, No. of poles: 16, 90°, Box |
| 1761692001 | SL-SMT3.5/17/90G 1.5SN | PCB plug-in connector, Male connectors, Reflow solder connection, Pitch: 3.50 mm, No. of poles: 17, 90°, Box |
| 1841780000 | SL-SMT3.5/17/90G 3.2SN SW BOX | PCB plug-in connector, Male connectors, Reflow solder connection, Pitch: 3.50 mm, No. of poles: 17, 90°, Box |
| 1761702001 | SL-SMT3.5/18/90G 1.5SN | PCB plug-in connector, Male connectors, Reflow solder connection, Pitch: 3.50 mm, No. of poles: 18, 90°, Box |
| 1841790000 | SL-SMT3.5/18/90G 3.2SN SW BOX | PCB plug-in connector, Male connectors, Reflow solder connection, Pitch: 3.50 mm, No. of poles: 18, 90°, Box |
| 1761712001 | SL-SMT3.5/19/90G 1.5SN | PCB plug-in connector, Male connectors, Reflow solder connection, Pitch: 3.50 mm, No. of poles: 19, 90°, Box |
| 1841800000 | SL-SMT3.5/19/90G 3.2SN SW BOX | PCB plug-in connector, Male connectors, Reflow solder connection, Pitch: 3.50 mm, No. of poles: 19, 90°, Box |
| 1761542001 | SL-SMT3.5/2/90G 1.5SN | PCB plug-in connector, Male connectors, Reflow solder connection, Pitch: 3.50 mm, No. of poles: 2, 90°, Box |
| 1841630000 | SL-SMT3.5/2/90G 3.2SN SW BOX | PCB plug-in connector, Male connectors, Reflow solder connection, Pitch: 3.50 mm, No. of poles: 2, 90°, Box |
| 1761722001 | SL-SMT3.5/20/90G 1.5SN | PCB plug-in connector, Male connectors, Reflow solder connection, Pitch: 3.50 mm, No. of poles: 20, 90°, Box |

| | | |
|------------|----------------------------------|---|
| 1841810000 | SL-SMT3.5/20/90G 3.2SN SW BOX | PCB plug-in connector, Male connectors, Reflow solder connection, Pitch: 3.50 mm, No. of poles: 20, 90°, Box |
| 1761732001 | SL-SMT3.5/21/90G 1.5SN | PCB plug-in connector, Male connectors, Reflow solder connection, Pitch: 3.50 mm, No. of poles: 21, 90°, Box |
| 1841820000 | SL-SMT3.5/21/90G 3.2SN SW BOX | PCB plug-in connector, Male connectors, Reflow solder connection, Pitch: 3.50 mm, No. of poles: 21, 90°, Box |
| 1761742001 | SL-SMT3.5/22/90G 1.5SN | PCB plug-in connector, Male connectors, Reflow solder connection, Pitch: 3.50 mm, No. of poles: 22, 90°, Box |
| 1841830000 | SL-SMT3.5/22/90G 3.2SN SW BOX | PCB plug-in connector, Male connectors, Reflow solder connection, Pitch: 3.50 mm, No. of poles: 22, 90°, Box |
| 1761752001 | SL-SMT3.5/23/90G 1.5SN | PCB plug-in connector, Male connectors, Reflow solder connection, Pitch: 3.50 mm, No. of poles: 23, 90°, Box |
| 1841840000 | SL-SMT3.5/23/90G 3.2SN SW BOX | PCB plug-in connector, Male connectors, Reflow solder connection, Pitch: 3.50 mm, No. of poles: 23, 90°, Box |
| 1761762001 | SL-SMT3.5/24/90G 1.5SN | PCB plug-in connector, Male connectors, Reflow solder connection, Pitch: 3.50 mm, No. of poles: 24, 90°, Box |
| 1841850000 | SL-SMT3.5/24/90G 3.2SN SW BOX | PCB plug-in connector, Male connectors, Reflow solder connection, Pitch: 3.50 mm, No. of poles: 24, 90°, Box |