






Pin headers SLD 5.08V/180B

new






Technical data	VDE	UL	CSA
Rated voltage (V)	250*	300	300
Rated current (A)	7	15	10

*Pollution severity 3 / Overvoltage category III

Additional technical data see page 217

Pin headers SLD 5.08R/90






Technical data	VDE	UL	CSA
Rated voltage (V)	250*	300	300
Rated current (A)	8	15	10

*Pollution severity 3 / Overvoltage category III

Additional technical data see page 216

Pin headers SLD 5.08R/180



Technical data	VDE	UL	CSA
Rated voltage (V)	250*	300	300
Rated current (A)	8	15	10

*Pollution severity 3 / Overvoltage category III

Additional technical data see page 216

Solder pin length

3.2 mm 4.5 mm

Color

Poles	Type	Part No.	Qty.
4	SLD 5.08V/4/180B	1726740000 1726970000	100
6	SLD 5.08V/6/180B	1726750000 1726980000	100
8	SLD 5.08V/8/180B	1726760000 1726990000	100
10	SLD 5.08V/10/180B	1726770000 1727000000	50
12	SLD 5.08V/12/180B	1726780000 1727010000	50
14	SLD 5.08V/14/180B	1726790000 1727020000	50
16	SLD 5.08V/16/180B	1726800000 1727030000	50
18	SLD 5.08V/18/180B	1726810000 1727040000	50
20	SLD 5.08V/20/180B	1726820000 1727050000	50
22	SLD 5.08V/22/180B	1726830000 1727060000	50
24	SLD 5.08V/24/180B	1726840000 1727070000	50
26	SLD 5.08V/26/180B	1726850000 1727080000	50
28	SLD 5.08V/28/180B	1726860000 1727090000	50
30	SLD 5.08V/30/180B	1726870000 1727100000	50
32	SLD 5.08V/32/180B	1726880000 1727110000	50
34	SLD 5.08V/34/180B	1726890000 1727120000	50
36	SLD 5.08V/36/180B	1726900000 1727130000	20
38	SLD 5.08V/38/180B	1726910000 1727140000	20
40	SLD 5.08V/40/180B	1726920000 1727150000	20
42	SLD 5.08V/42/180B	1726930000 1727160000	20
44	SLD 5.08V/44/180B	1726940000 1727170000	20
46	SLD 5.08V/46/180B	1726950000 1727180000	20
48	SLD 5.08V/48/180B	1726960000 1727190000	20

Accessories	Page
Mounting	187**
Marking	190
Coding	193
Miscellaneous	-

Solder pin length

4.5 mm 4.5 mm

Color

Poles	Type	Part No.	Part No.	Qty.
4	SLD 5.08R/4/90	1602020000 1711450000	50	
6	SLD 5.08R/6/90	1602030000 1675320000	50	
8	SLD 5.08R/8/90	1602040000 1675330000	50	
10	SLD 5.08R/10/90	1602050000 1711480000	50	
12	SLD 5.08R/12/90	1602060000 1711490000	50	
14	SLD 5.08R/14/90	1602070000 1711500000	20	
16	SLD 5.08R/16/90	1602080000 1711510000	20	
18	SLD 5.08R/18/90	1602090000 1711520000	20	
20	SLD 5.08R/20/90	1602100000 1711530000	20	
22	SLD 5.08R/22/90	1602110000 1711540000	10	
24	SLD 5.08R/24/90	1602120000 1711550000	10	
26	SLD 5.08R/26/90	1602130000 1711560000	10	
28	SLD 5.08R/28/90	1602140000 1711570000	10	
30	SLD 5.08R/30/90	1602150000 1711580000	10	
32	SLD 5.08R/32/90	1602160000 1711590000	10	
34	SLD 5.08R/34/90	1602170000 1711600000	10	
36	SLD 5.08R/36/90	1602180000 1711610000	10	
38	SLD 5.08R/38/90	1602190000 1711620000	10	
40	SLD 5.08R/40/90	1602200000 1711630000	10	
42	SLD 5.08R/42/90	1602210000 1711640000	10	
44	SLD 5.08R/44/90	1602220000 1711650000	10	
46	SLD 5.08R/46/90	1602230000 1711660000	10	
48	SLD 5.08R/48/90	1602240000 1711670000	10	

Accessories	Page
Mounting	-
Marking	190
Coding	192, 193
Miscellaneous	-

Solder pin length

4.5 mm 4.5 mm

Color

Poles	Type	Part No.	Part No.	Qty.
4	SLD 5.08R/4/180	1602620000 1711680000	50	
6	SLD 5.08R/6/180	1602630000 1711690000	50	
8	SLD 5.08R/8/180	1602640000 1711700000	50	
10	SLD 5.08R/10/180	1602650000 1711710000	50	
12	SLD 5.08R/12/180	1602660000 1711720000	50	
14	SLD 5.08R/14/180	1602670000 1711730000	20	
16	SLD 5.08R/16/180	1602680000 1676730000	20	
18	SLD 5.08R/18/180	1602690000 1711750000	20	
20	SLD 5.08R/20/180	1602700000 1711760000	20	
22	SLD 5.08R/22/180	1602710000 1711770000	10	
24	SLD 5.08R/24/180	1602720000 1711780000	10	
26	SLD 5.08R/26/180	1602730000 1711790000	10	
28	SLD 5.08R/28/180	1602740000 1711800000	10	
30	SLD 5.08R/30/180	1602750000 1711810000	10	
32	SLD 5.08R/32/180	1602760000 1711820000	10	
34	SLD 5.08R/34/180	1602770000 1711830000	10	
36	SLD 5.08R/36/180	1602780000 1711840000	10	
38	SLD 5.08R/38/180	1602790000 1711850000	10	
40	SLD 5.08R/40/180	1602800000 1711860000	10	
42	SLD 5.08R/42/180	1602810000 1711870000	10	
44	SLD 5.08R/44/180	1602820000 1711880000	10	
46	SLD 5.08R/46/180	1602830000 1711890000	10	
48	SLD 5.08R/48/180	1602840000 1711900000	10	

Accessories	Page
Mounting	-
Marking	190
Coding	192, 193
Miscellaneous	-

**See Note, page 187