

# RC-12S2N12YR00 - Device connector front mounting with knurled nut



1599995

<https://www.phoenixcontact.com/us/products/1599995>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



M23, Device connector front mounting with knurled nut, series: RC, straight, shielded: yes, Screw locking mechanism, No. of pos.: 12, Direction of rotation: Counter direction, contact connection type: Socket, Solder cup, Radial O-ring, 4x Ø 3.2, coding: N

## Commercial data

Item number	1599995
Packing unit	1 pc
Minimum order quantity	20 pc
Note	Made to order (non-returnable)
Sales key	AB31
Product key	ABRAFO
GTIN	4046356228114
Weight per piece (including packing)	55.99 g
Weight per piece (excluding packing)	49.28 g
Customs tariff number	85366990
Country of origin	DE

# RC-12S2N12YR00 - Device connector front mounting with knurled nut



1599995

<https://www.phoenixcontact.com/us/products/1599995>

## Technical data

### Product properties

Product type	Circular connectors (device side)
--------------	-----------------------------------

### Connector

#### Insulating body

Coding	N
Insertion/withdrawal cycles	50
Connection method	Solder cup
Contact switching type	Socket
Application	Signal
Number of positions	12
Direction of rotation	Counter direction
Connection profile	12
Contact diameter <b>Power contacts</b>	1 mm
Litz wire cross-section <b>Power contacts</b> min.	0.08 mm <sup>2</sup>
Litz wire cross-section <b>Power contacts</b> max.	1 mm <sup>2</sup>
Rated current <b>Power contacts</b>	8 A
Rated voltage	48 V AC
	74 V DC
Rated surge voltage	1.5 kV
Overtoltage category	III
Degree of pollution	3

#### Housing

Order information:	Order contact inserts separately
Housing material	Metal
Type of locking	Screw locking mechanism
Pg screw connection	none
Degree of protection (plugged in)	IP67
Thread type	M23

# RC-12S2N12YR00 - Device connector front mounting with knurled nut




1599995

<https://www.phoenixcontact.com/us/products/1599995>

## Drawings

Schematic diagram



Connector pin assignment

# RC-12S2N12YR00 - Device connector front mounting with knurled nut



1599995

<https://www.phoenixcontact.com/us/products/1599995>

## Classifications

### ECLASS

ECLASS-11.0	27440102
-------------	----------

### UNSPSC

UNSPSC 21.0	39121413
-------------	----------

# RC-12S2N12YR00 - Device connector front mounting with knurled nut



1599995

<https://www.phoenixcontact.com/us/products/1599995>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

### China RoHS

Environment friendly use period (EFUP)	EFUP-50  An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.
--	--

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
-------------------------------------	----------------------

# RC-12S2N12YR00 - Device connector front mounting with knurled nut



1599995

<https://www.phoenixcontact.com/us/products/1599995>

## Accessories

### RC-Z2062 - Metal protective cap

1604228

<https://www.phoenixcontact.com/us/products/1604228>

Metal protective cap, M23, series: RC, UC, RF, SF, NC, RM, Alternative product in accordance with RoHS II without Exemption 6c (Pb < 0.1 %) item no.: 1241732



---

Phoenix Contact 2024 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)