

HC-4 Product Details

**HC-4**

(4-1618274-9)

TE Internal Number: 4-1618274-9



High Voltage Relays

[Not EU RoHS or ELV Compliant](#)**Product Highlights:**

- Contact Arrangement = 1 Form B, SPST-NC, 1 N/C, 1 Form A, SPST-NO, 1 N/O, 1 Form C, SPDT, 1 C/O
- Power Switching = Make Only, Yes, No
- Contact Current Rating = 0 - 15 Amps.
- Not RF Rated
- Coil Voltage = 26.5 VDC

[View all Features](#)**Quick Links**

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

 [Add to My Part List](#) [Request Sample](#) [Find Similar Products](#) [Buy Product](#)

Documentation & Additional Information

Product Drawings:

- None Available

Additional Information:

- [Product Line Information](#)

Catalog Pages/Data Sheets:

- None Available

Related Products:

- [Tooling](#)

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Termination Style](#) = Turret Terminal

Body Related Features:

- [Mount Style](#) = Non-Flanged

Electrical Characteristics:

- [Contact Current Rating \(Amps.\)](#) = 0 - 15
- [RF Rated](#) = No
- [Coil Voltage \(VDC\)](#) = 26.5
- [Voltage, Max. \(VDC\)](#) = 0 - 8000
- Current, Carry Only = Yes

Configuration Related Features:

- [Contact Arrangement](#) = 1 Form B, SPST-NC, 1 N/C, 1 Form A, SPST-NO, 1 N/O, 1 Form C, SPDT, 1 C/O
- [Power Switching](#) = Make Only, Yes, No
- [Economizer](#) = Without

Termination Related Features:

- [High Voltage Connection \(Power\)](#) = Bifurcated Terminals
- [High Voltage Connection \(Coil\)](#) = Turret Terminals
- [Auxiliary Contacts](#) = Without

Industry Standards:

- [RoHS/ELV Compliance](#) = Not ELV/RoHS compliant
- [Lead Free Solder Processes](#) = Not suitable for lead free processing

Other:

- Brand = Kilovac

Corporate Information[Who We Are](#)[Investors](#)[News Room](#)[Supplier Portal](#)[Careers](#)**Quick Links**[Check Distributor Inventory](#)[Cross Reference](#)[Find Documents & Drawings](#)[Product Compliance Support Center](#)[Site Map](#)**Customer Support**[Email or Chat with Us](#)[Find a Phone Number](#)[Search Knowledge Base](#)[Manage Your Account](#)