





1986469-5 Product Details



1986469-5

TE Internal Number: 1986469-5



Europa Terminal Blocks

 Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- 14.50 mm Centerline
- Number of Circuits = 5
- Wire Range = 2.00-14.00; [14-6] mm [AWG]
- With Wire Protection
- Integrated Fuse = Without

[View all Features](#)

Quick Links

- ▶ [Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#) [Request Sample](#) [Find Similar Products](#) [Buy Product](#)

Documentation & Additional Information

Documents are temporarily unavailable. We are working hard to correct the problem. Please try again later.

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Integrated Fuse](#) = Without
- Color = Brown
- Screw Size = M5

Electrical Characteristics:

- Current Rating (A) = 65
- Voltage Rating (VAC) = 600
- Wire Protector Material = Stainless Steel

Body Features:

- [Wire Range \(mm \[AWG\]\)](#) = 2.00-14.00; [14-6]
- [Wire Protection](#) = With
- [Ground](#) = Without
- Screw Material = Steel
- Screw Plating = Zinc Chromate

Contact Features:

- Contact Base Material = Brass
- Contact Plating, Mating Area, Material = Tin

Housing Features:

- [Centerline \(mm \[in\]\)](#) = 14.50 [0.571]
- Housing Material = Polyamide 6

Configuration Features:

- [Number of Circuits](#) = 5

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant
- UL Flammability Rating = UL 94V-0

Conditions for Usage:

- [Temperature Range \(°C\)](#) = 150

Other:

- [Series](#) = TSB2000
- Brand = TE Connectivity

Corporate Information

[About TE](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)
[Careers](#)
[Terms & Conditions](#)
[Privacy Policy](#)
[AODA Accessibility Policy](#)
[AODA Multi-Year Accessibility Plan](#)

Quick Links

[Distributor Inventory](#)
[Product Cross Reference](#)
[Documents & Drawings](#)
[Product Compliance Support Center](#)
[Site Map](#)

Customer Support

[Email or Chat With Us](#)
[Find a Phone Number](#)
[Knowledge Base](#)
[Manage Your Account](#)

Keep Me Informed



