

# RC-22P2000 - Crimp contact



1603321

<https://www.phoenixcontact.com/us/products/1603321>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Crimp contact, Pin, rolled, Single contact, contact diameter: 1 mm, crimp range: 0.22 mm<sup>2</sup> ... 0.56 mm<sup>2</sup>, Single contact, Item is lead-free in accordance with RoHS II without Exemption 6c (Pb < 0.1 %)

## Your advantages

- Crimping connection: vibration- and temperature-resistant assembly
- High tensile strength of the connection
- Low contact resistance
- Easy production monitoring
- Variable production run startup, thanks to full or semi-automation

## Commercial data

Item number	1603321
Packing unit	100 pc
Minimum order quantity	100 pc
Sales key	AB36
Product key	ABRECA
Catalog page	Page 78 (C-2-2019)
GTIN	4046356244909
Weight per piece (including packing)	0.101 g
Weight per piece (excluding packing)	0.1 g
Customs tariff number	85366990
Country of origin	DE

# RC-22P2000 - Crimp contact

1603321

<https://www.phoenixcontact.com/us/products/1603321>



## Technical data

### Notes

Order information:	Single contact
--------------------	----------------

### Product properties

Product type	Crimp contact
Contact material type	rolled

### Data management status

Article revision	00
------------------	----

### Connection data

Connection method	Crimp connection
Contact connection type	Pin
Conductor cross section	0.22 mm <sup>2</sup> ... 0.56 mm <sup>2</sup>

### Material specifications

Contact surface	Gold
Contact material	Cu alloy

### Dimensions

Mechanical characteristics	
Contact diameter	1 mm

### Mechanical properties

Mechanical data	
Insertion/withdrawal cycles	100

# RC-22P2000 - Crimp contact

1603321

<https://www.phoenixcontact.com/us/products/1603321>



## Classifications

### ECLASS

ECLASS-11.0	27440204
ECLASS-12.0	27440204
ECLASS-13.0	27440204

### ETIM

ETIM 9.0	EC000796
----------	----------

### UNSPSC

UNSPSC 21.0	39121500
-------------	----------

# RC-22P2000 - Crimp contact

1603321

<https://www.phoenixcontact.com/us/products/1603321>



## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2024 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)