

ES-BBC-MF1 - Panel-mount frame



1155603

<https://www.phoenixcontact.com/us/products/1155603>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Panel-mount frame, Range of articles: BBC, design: Panel-mount frame, housing material: PA-GF, color: black

Commercial data

Item number	1155603
Packing unit	12 pc
Minimum order quantity	12 pc
Sales key	AB04
Product key	ABLDAC
GTIN	4063151156992
Weight per piece (including packing)	35.61 g
Weight per piece (excluding packing)	22.22 g
Customs tariff number	85389099
Country of origin	DE

ES-BBC-MF1 - Panel-mount frame

1155603

<https://www.phoenixcontact.com/us/products/1155603>



Technical data

Product properties

Product type	Connectors for energy storage
Product family	BBC
Type	Panel-mount frame
Number of slots	1

Data management status

Article revision	04
------------------	----

Dimensions

Width	68 mm
Height	50.5 mm
Length	41 mm

Material specifications

Color	black
Color of the housing part	black
Material	Polyamide
Flammability rating according to UL 94	V0
Housing material	PA-GF

Cable/line

Halogen-free	yes
--------------	-----

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	1
-----------------------------	---

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-10 °C ... 50 °C
---------------------------------	------------------

ES-BBC-MF1 - Panel-mount frame



1155603

<https://www.phoenixcontact.com/us/products/1155603>

Classifications

ECLASS

ECLASS-11.0	27440390
ECLASS-12.0	27440390
ECLASS-13.0	27440390

ETIM

ETIM 9.0	EC004746
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

ES-BBC-MF1 - Panel-mount frame



1155603
<https://www.phoenixcontact.com/us/products/1155603>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2024 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com