

# HC-COM-CHWS-1TTM25-EL-AL - Housing



1078595

<https://www.phoenixcontact.com/us/products/1078595>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Coupling housings COM, with single locking latch, material: Die-cast aluminum, salt water resistant, cable outlets: 1, straight, 1x M25, height: 68 mm, cable gland: none, Standard

## Your advantages

- Good shielding in the event of electromagnetic interference

## Commercial data

Item number	1078595
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BF59
Product key	BF7APP
Catalog page	Page 653 (C-2-2019)
GTIN	4055626794136
Weight per piece (including packing)	87.8 g
Weight per piece (excluding packing)	22.22 g
Customs tariff number	85389099
Country of origin	CN

## Technical data


### Product properties

Product type	Housing with locking latch
Housing type	Coupling housings
Product family	HC-COM
Application	Standard
Type	COM
No. of cable outlets	1
Type of the screw connection	1x M25
Type	Tall design
Cable outlet	straight
Pg screw connection	none

### Data management status

Article revision	01
------------------	----

### Dimensions

Dimensional drawing	
Width	39 mm
Height	68 mm
Length	48.8 mm

### Material specifications

Flammability rating according to UL 94	V0 (Interlock)
Seal material	NBR
Housing material	Die-cast aluminum, salt water resistant
Locking latch material	PA

### Mechanical properties

#### Mechanical data

Type of the screw connection	1x M25
Locking type	Latch

### Environmental and real-life conditions

#### Ambient conditions

Degree of protection	IP66
Impact strength	IK06

# HC-COM-CHWS-1TTM25-EL-AL - Housing

1078595

<https://www.phoenixcontact.com/us/products/1078595>



Ambient temperature (operation)	-40 °C ... 125 °C
---------------------------------	-------------------

# HC-COM-CHWS-1TTM25-EL-AL - Housing


1078595

<https://www.phoenixcontact.com/us/products/1078595>



## Drawings

Dimensional drawing




1078595


<https://www.phoenixcontact.com/us/products/1078595>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1078595>



**cUL Recognized**  
Approval ID: E255026



**UL Recognized**  
Approval ID: E255026

**cULus Recognized**

# HC-COM-CHWS-1TTM25-EL-AL - Housing



1078595

<https://www.phoenixcontact.com/us/products/1078595>

## Classifications

### ECLASS

ECLASS-11.0	27440202
ECLASS-12.0	27440202
ECLASS-13.0	27440202

### ETIM

ETIM 9.0	EC000437
----------	----------

### UNSPSC

UNSPSC 21.0	31261500
-------------	----------

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%