

HDMI All-in-One Keystone/Panel Mount Coupler (F/F), Black, TAA

MODEL NUMBER: P164-000-KP-BK



Connects two HDMI cables to create one longer cable. Snaps into keystone cutout of a wallplate or panel. Or use the included panel mount adapter for installation in a podium or kiosk.

Description

Strengthen your high-definition audio/video application with the P164-000-KP-BK HDMI All-in-One Keystone/Panel Mount Coupler. It connects two HDMI cables to create one longer connection, and its keystone design snaps easily into the cutout of a wallplate or panel. It comes with an optional panel mount adapter for securing the coupler to a podium or kiosk. Compatible with all HDMI cables, this coupler features molded gold-plated connectors for optimal signal transfer.

Features

Strengthens Your High-Definition Connection

- Connects 2 HDMI cables for a longer cable run
- Keystone design for easy snap-in installation in wallplate or panel
- Includes panel mount adapter for installation in podium or kiosk
- Molded gold-plated connectors for optimum signal transfer
- Hides components out of sight to eliminate cable clutter
- Compatible with all HDMI cables

Specifications

OVERVIEW	
UPC Code	037332195722
Technology	HDMI
VIDEO	
Max Supported Video Resolution	3840 x 2160 (4K) @ 60Hz

Highlights

- Molded gold-plated connectors for optimal signal transfer
- Panel mount adapter for securing to podium or kiosk
- Keystone design for use with standard data wallplate
- Compatible with all HDMI cables

Package Includes

- P164-000-KP-BK HDMI All-in-One Keystone/Panel Mount Coupler (F/F), Black



Powering Business Worldwide

TRIPP LITE
SERIES

CONNECTIONS	
Side A - Connector 1	HDMI (FEMALE)
Side B - Connector 1	HDMI (FEMALE)
PHYSICAL	
Color	Black
Shipping Dimensions (hwd / in.)	0.50 x 7.00 x 9.40
Shipping Dimensions (hwd / cm)	1.27 x 17.78 x 23.88
Shipping Weight (lbs.)	0.06
Shipping Weight (kg)	0.03
Unit Dimensions (hwd / in.)	0.580 x 0.640 x 1.140
Unit Dimensions (hwd / mm)	14.7 x 16.3 x 29
FEATURES & SPECIFICATIONS	
IP68 Rated	No
IP20 Rated	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; REACH; Trade Agreements Act (TAA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.