Product Update Amphenol Pcd




Luminus Series

Shell Size 5: Screw Mount Cradle & Tape Mount Cradle

Amphenol Pcd is pleased to announce the latest addition to our Luminus accessories; the SJS25700 and SJS257100 cradles for mounting shell size 5

connectors. These two cradles offer the option of either convenient tape mounting styles or enhanced security of the screw mount style. The tape mount style uses the 3M 5958FR tape for superior long lasting adhesion under a wide range of operating conditions. The screw mount style allows the use of industry standard 4/40 imperial or M3 metric mounting hardware. Both cradles have tie wrap features on the tines, for those customers that desire the redundant security of tie wraps or nomex string.

Available 11/1



(*Specifications on back)

John Whittaker

jwhittaker@amphenolpcd.com Office: 978.624.3447 Mobile: 978.882.3609

Hilary Juntwait

hjuntwait@amphenolpcd.com Office: 978.624.3459









Materials & Specifications

	Twist & Lock
Materials (Custom Material Available)	Insulator Body: Polyamide 6/6 (Nylon)
	Grommet: Silicone Rubber
	Contact Retainer: Stainless Steel
	Contacts: Copper Alloy Gold Plated
Temperature Range	-65°C to 125°C
Temperature Life	500 hours @ 85°C
Insulation	5000 MΩ Min. @ 500 VDC
Resistance	
Dielectric Withstanding	1500 VAC, 60 Hz @ Sea Level, 1ma
	300 VAC, 60 Hz @ 70,000 ft, 2 ma
	300 VAC, 60 Hz @ 100,000 ft, 2 ma
Durability	500 mating cycles
Altitude Immersion	5% salt solution
	5000Mohms @ 1500 VAC, sea level
	5000Mohms @ 300 VAC, 70k ft
	5000Mohms @ 300 VAC, 100k ft
Temperature Cycling	5(1) Hour Cycles: -65°C to 125°C

Thermal Shock	-65°C to 200°C
Vibration	30G Sinusoidal; 43.96G Random
Shock	300G, 3msec, Half-Sine
Salt Spray	5% Salt Spray @ 95°C for 48 Hours
Humidity	10 Days @ 25˚C to 65˚C, 90% - 95% RH
Fluid Immersion	Lubricating Oil per Mil-Prf-7808
	Cleaning Compound per Mil-Prf-87937, Alkaline Base
	Isopropyl Alcohol & Mineral Spirit Solution
	Skydrol Hydraulic Fluid
	Hydraulic Fluids per MIL-PRF-83282 MIL-PRF-87257
	Ethylene Glycol
	Propylene Glycol
	Aviation Jet A
Seal Rating	IP67
Flammability	UL94, V0.
	DOTG section 26.6.2 & 26.6.3
	FAR Part 25 App F Part I
RoHS & REACH Compliance	Yes


Related Products Amphenol Pcd



Rayzor Series



Pegasus Series NEW



Relay Sockets & Junction Modules







