




CONNECTORS

SMA CONNECTORS



✓ Active

↓ **PRODUCT DRAWING**
English

TE CONNECTIVITY (TE)

2034 8052 92

AMP | SM , SMA

1051998-1

TE Internal Number: 1051998-1

Mil-Spec: M39012/59-3502

Alias ID: 2034-8052-92

Always EU RoHS/ELV Compliant

Applies To **Coaxial Cable**

Panel Mount **With**

Body Material **Stainless Steel**

Body Plating Finish **Passivated**

Panel Mount Retention Type **Bulkhead**



Product Drawings

OSM BULKHEAD FEEDTHRU CABLE JACK-CRIMP ATTACHMENT

PDF (**TIFF AVAILABLE**)
English

OSM BULKHEAD FEEDTHRU CABLE JACK-CRIMP ATTACHMENT

PDF (**TIFF AVAILABLE**)
English

Instruction Sheets

Instruction Sheet (U.S.)

SMA Bulkhead Feedthrough Cable Jack Solder Attachment 1051998-1

PDF
English

Please review product documents or [contact us](#) for the latest agency approval information. Please Note: Use the Product Drawing for all design activity.

Product Type Features

Applies To

Coaxial Cable

RF Connector Type

SMA

	Connector Style	Jack
	Cable Type	RG 142, RG 223, RG 400
	Product Type	Connector - RF
	Shrink Tubing	Without
	Dielectric Material	PTFE
	Retractable Collar	Without
	Grade	Military
	Sealed	Panel
Configuration Features	Snap-Lock	Without
Electrical Characteristics	50 Ohm	Yes
	75 Ohm	No
	Impedance (Ω)	50
Signal Characteristics	Frequency (GHz)	12.4
Body Features	Body Material	Stainless Steel
	Body Plating Finish	Passivated
	Body Style	Straight
	Gasket Material	Silicone Rubber
	Ferrule Material	Copper Alloy
	Ferrule Plating Material	Gold
Contact Features	Captivation Method	Mechanical
	Center Contact Plating Material	Gold
	Center Contact	With
	Center Contact Material	Beryllium Copper
	Captivated Contacts	With
Termination Features	Cable Termination Type	Crimp
	Crimp Type	Hex
Mechanical Attachment	Panel Mount	With
	Panel Mount Retention Type	Bulkhead
	Lockwasher Plating Finish	Passivated
	Polarized	No

	Lockwasher Material	Stainless Steel
	Panel Attachment Style	Rear Mount
	Mounting Nut Material	Stainless Steel

Dimensions	Length	26.3 mm [1.035 in]
------------	--------	----------------------

Industry Standards	Military Category	D
--------------------	-------------------	---

Packaging Features	Packaging Method	Package
--------------------	------------------	---------

Product Compliance	<div>Statement of Compliance</div> <div>PDF</div> <div>VIEW ALL PRODUCT COMPLIANCE</div>	
--------------------	--	--

