




1393454-6 Product Details



1393454-6

TE Internal Number: 1393454-6

[Active](#)

[View 3D PDF](#)

Timer Connectors

[Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- Accessory
- Accessory Type = Backshell/Cable Clamp
- Type of Connector = 1.6/2.8, Hybrid Timer, JPT/Micro Timer 2
- 52 Positions
- PBT Material

[View all Features](#)

Quick Links

- ▶ [Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#)



[Request Sample](#)



[Find Similar Products](#)



[Buy Product](#)

Documentation & Additional Information

Product Drawings:

- [52 pol. Abdeckkappe fur 80 pol. Motorstecker \(1\) \(PDF, English\)](#)
- [52 pol. Abdeckkappe fur 80 pol. Motorstecker \(2\) \(PDF, English\)](#)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files: (CAD Format & Compression Information)

- [2D Drawing \(DXF, Version A1\)](#)
- [3D Model \(IGES, Version A1\)](#)
- [3D Model \(STEP, Version A1\)](#)

[List all Documents](#)

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Product Type = Accessory
- Accessory Type = Backshell/Cable Clamp
- [Type of Connector](#) = 1.6/2.8, Hybrid Timer, JPT/Micro Timer 2
- Color = Black

Body Features:

- Material = PBT
- Cable Exit Angle = 90°

Configuration Features:

- Number of Positions = 52

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

Conditions for Usage:

- For Use With = MT-2/JPT Connector, 1393450-1

Other:

- Brand = AMP
- Comment = Customer marking, see drawing.

Corporate Information

[About TE](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)
[Careers](#)
[Terms & Conditions](#)
[Privacy Policy](#)
[AODA Accessibility Policy](#)

Quick Links

[Distributor Inventory](#)
[Product Cross Reference](#)
[Documents & Drawings](#)
[Product Compliance Support Center](#)
[Site Map](#)

Customer Support

[Email or Chat With Us](#)
[Find a Phone Number](#)
[Knowledge Base](#)
[Manage Your Account](#)

Keep Me Informed



