





141993-3 Product Details



141993-3

TE Internal Number: 141993-3



Positive Lock Connectors



Converted to EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- Contact
- Contact Type = Socket
- Mating Area Interface Dimensions = 5.00 x 0.80 mm
- Applies To Wire/Cable
- Line = AMP POSITIVE LOCK Mark III

[View all Features](#)

Quick Links

- ▶ [Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- [CLIP SECURITE DROIT 5 MM A VERROUILLAGE POSITIF](#) (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- [CLIP DROIT DE SECURITE POSITIVE LOCK MARK III](#) (PDF, French)

Instruction Sheets:

- None Available

CAD Files: (CAD Format & Compression Information)

- [2D Drawing](#) (DXF, Version H)
- [3D Model](#) (IGES, Version H)
- [3D Model](#) (STEP, Version H)

[List all Documents](#)

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Product Type](#) = Contact
- [Receptacle Style](#) = Straight
- [Finish](#) = Pre-Tin
- [Keyed](#) = No

Dimensions:

- [Mating Area Interface Dimensions](#) (mm [in]) = 5.00 x 0.80 [.197 x .031]
- [Insulation Diameter](#) (mm [in]) = 4.88 [.192] Max.

Body Features:

- [Wire Range](#) (mm [AWG]) = 3.00-6.00² [12-10]
- [Material](#) = Brass
- [Position Keyed](#) = None

Contact Features:

- Contact Type = Socket

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Converted to comply with RoHS directive

Conditions for Usage:

- Applies To = Wire/Cable

Packaging Features:

- [Packaging Method](#) = Strip

Other:

- [Line](#) = AMP POSITIVE LOCK Mark III
- Brand = AMP

Corporate Information

[About TE](#)

[Investors](#)

[News Room](#)

[Supplier Portal](#)

Quick Links

[Distributor Inventory](#)

[Product Cross Reference](#)

[Documents & Drawings](#)

[Product Compliance Support Center](#)

Customer Support

[Email or Chat With Us](#)

[Find a Phone Number](#)

[Knowledge Base](#)

[Manage Your Account](#)

Keep Me Informed



