



[Home](#) > [Products](#) > [By Type](#) > [Relays](#) > [Product Feature Selector](#) > Product Details

PD90XB57 Product Details



PD90XB57
(7-1618013-3)

TE Internal Number: 7-1618013-3

Active

High Voltage Relays

[Not EU RoHS or ELV Compliant](#)

Product Highlights:

- Contact Arrangement = 1 Form A, SPST-NO, 1 N/O
- Power Switching = Make Only, Yes, No
- Contact Current Rating = 0 - 90 Amps.
- Not RF Rated
- Coil Voltage = 24 VDC

[View all Features](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

[Add to My Part List](#)

[Request Sample](#)

[Find Similar Products](#)

[Buy Product](#)

Documentation & Additional Information

Product Drawings:

- None Available

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Termination Style](#) = Stud Terminal

Electrical Characteristics:

- [Contact Current Rating \(Amps.\)](#) = 0 - 90
- [RF Rated](#) = No
- [Coil Voltage \(VDC\)](#) = 24
- [Voltage, Max. \(VDC\)](#) = 0 - 1800
- Current, Carry Only = Yes

Termination Related Features:

- [High Voltage Connection \(Power\)](#) = Stud Terminal
- [High Voltage Connection \(Coil\)](#) = Stud Terminal
- [Auxiliary Contacts](#) = Without

Body Related Features:

- [Mount Style](#) = Panel

Configuration Related Features:

- [Contact Arrangement](#) = 1 Form A, SPST-NO, 1 N/O
- [Power Switching](#) = Make Only, Yes, No
- [Economizer](#) = Without

Industry Standards:

- [RoHS/ELV Compliance](#) = Not ELV/RoHS compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process

Other:

- Brand = Kilovac

Corporate Information

[Who We Are](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)
[Careers](#)

Quick Links

[Check Distributor Inventory](#)
[Cross Reference](#)
[Find Documents & Drawings](#)
[Product Compliance Support Center](#)
[Site Map](#)

Customer Support

[Email or Chat with Us](#)
[Find a Phone Number](#)
[Search Knowledge Base](#)
[Manage Your Account](#)