


[Home](#) > [Products](#) > [By Type](#) > [Relays](#) > [Product Feature Selector](#) > Product Details

## FCA-410-1517M Product Details



**FCA-410-1517M**  
(1617754)

TE Internal Number: 1617754

 **Active**

### Military/Aerospace Mid-Range Relays

[Not EU RoHS or ELV Compliant](#)

#### Product Highlights:

- FCA 10-25 Amp Relay Series
- DC Actuating System
- Coil Voltage = 28 VDC
- Contact Arrangement = 4 Form C, 4PDT, 4 C/O
- Current Rating = 10 Amps.

[View all Features](#)

#### Quick Links

[Check Pricing & Availability](#)  
[Search for Tooling](#)  
[Product Feature Selector](#)  
[Contact Us About This Product](#)

 [Add to My Part List](#)
 [Request Sample](#)
 [Find Similar Products](#)
 [Buy Product](#)

### Documentation & Additional Information

#### Product Drawings:

- None Available

#### Catalog Pages/Data Sheets:

- [RELAY](#) (PDF, English)

#### Product Specifications:

- None Available

#### Application Specifications:

- None Available

#### Instruction Sheets:

- None Available

#### CAD Files:

- None Available

#### Additional Information:

- [Product Line Information](#)

#### Related Products:

- [Tooling](#)

[List all Documents](#)

### Product Features (Please use the Product Drawing for all design activity)

#### Product Type Features:

- [Terminal Configuration](#) = Solder Pins

#### Electrical Characteristics:

- [Actuating System](#) = DC
- [Coil Voltage \(VDC\)](#) = 28
- [Current Rating \(Amps.\)](#) = 10

#### Termination Related Features:

- [Terminal Plating](#) = Tin-Lead
- Auxiliary Contacts = Without

#### Body Related Features:

- Series = FCA 10-25 Amp Relay
- Mount Type = No Brackets

#### Configuration Related Features:

- [Contact Arrangement](#) = 4 Form C, 4PDT, 4 C/O
- [Coil Suppression Diode](#) = Without
- Coil Magnetic System = Polarized, Monostable

#### Industry Standards:

- Government/Industry Qualification = Yes
- Government/Industry Part Number = M83536/15-017M
- [RoHS/ELV Compliance](#) = Not ELV/RoHS compliant
- [Lead Free Solder Processes](#) = Not suitable for lead free processing

#### Other:

- Brand = CII

### Corporate Information

[Who We Are](#)  
[Investors](#)  
[News Room](#)  
[Supplier Portal](#)  
[Careers](#)

### Quick Links

[Check Distributor Inventory](#)  
[Cross Reference](#)  
[Find Documents & Drawings](#)  
[Product Compliance Support Center](#)  
[Site Map](#)

### Customer Support

[Email or Chat with Us](#)  
[Find a Phone Number](#)  
[Search Knowledge Base](#)  
[Manage Your Account](#)