

8		7		6		5		4		3		2		1										
RoHS								REV	ECN NO.		DESRIPTION		DESIGN		APPROVAL		DATE							
								A1	NEW		更换图框						2024.05.24							
E																	E							
D	P1 100±3 3.0±0.5脱皮浸锡 ① 3.0±0.5脱皮浸锡 P2																D							
C																	C							
B	技术要求： 1.1.端子铆接牢固，无松动，脱落等现象； 1.2.线材印字清晰，无破损划伤； 2.外观要求按品质管理部检验标准执行 3.包装要求按包装作业指引或客户指定包装要求																B							
A					<table><tr><td>X.±0.50</td><td>X.°±</td></tr><tr><td>.X±0.25</td><td>.X°±</td></tr><tr><td>.XX±0.15</td><td>.XX°±</td></tr><tr><td>.XXX±0.10</td><td>.XXX°±</td></tr><tr><td>UNITS:</td><td>mm</td></tr></table>		X.±0.50	X.°±	.X±0.25	.X°±	.XX±0.15	.XX°±	.XXX±0.10	.XXX°±	UNITS:	mm	PART NO: XF7126		XFCN兴飞连接器				A	
X.±0.50	X.°±																							
.X±0.25	.X°±																							
.XX±0.15	.XX°±																							
.XXX±0.10	.XXX°±																							
UNITS:	mm																							
<table><tr><td>①</td><td>线材</td><td>UL1007 22#红色</td><td>1PCS</td></tr><tr><td>序号</td><td>部件</td><td>线材 端子（部件） 胶壳</td><td>数量</td></tr><tr><td>NO.</td><td>PARTS</td><td>Cable, Terminal (Part) Housing</td><td>Quantity</td></tr></table>				①	线材	UL1007 22#红色	1PCS	序号	部件	线材 端子（部件） 胶壳	数量	NO.	PARTS	Cable, Terminal (Part) Housing	Quantity	THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF XFCN AND SHALL NOT BE REPRODUCED,COPIED OR CUED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF XFCN		TITLE: UL1007/22 红色 L=100 双端上锡3.0MM		0769-82001899				A
				①	线材	UL1007 22#红色	1PCS																	
序号	部件	线材 端子（部件） 胶壳	数量																					
NO.	PARTS	Cable, Terminal (Part) Housing	Quantity																					
DWG NO: /		www.xfconn.com																						
物料明细表 Material list						APPD		Chen ZhiQiang		VIEW		④		A										
						CHKD		Liu Wei		SCALE		SHEET		REV										
						DATE		2024.11.02		NONE		1/1		A1										
8		7		6		5		4		3		2		1										