




#### General ordering data

|                  |                               |
|------------------|-------------------------------|
| Order No.        | 1842240000                    |
| Part designation | SL-SMT3.5/18/90F 3.2SN SW BOX |
| Version          | , No. of poles: 18, Box       |
| EAN              | 4032248353590                 |
| Qty.             | 20 pc(s).                     |

#### System parameters

|                   |            |
|-------------------|------------|
| No. of poles      | 18         |
| Solder pin length | 3.2 mm     |
| L1 in mm          | 59.5 mm    |
| L1 in inch        | 2.343 inch |

#### Material data

|                 |                     |
|-----------------|---------------------|
| Colour          | black               |
| colour chart    | Similar to RAL 9011 |
| Contact surface | tinned              |

#### DIN IEC rating data

|                                                             |       |
|-------------------------------------------------------------|-------|
| Rated voltage for overvoltage class/pollution severity II/2 | 320 V |
|-------------------------------------------------------------|-------|

#### CSA rating data

|                             |       |
|-----------------------------|-------|
| Rated voltage (Use group D) | 300 V |
| Rated current (Use group D) | 10 A  |

#### UL 1059 rating data

|                             |       |
|-----------------------------|-------|
| Rated voltage (Use group D) | 300 V |
| Rated current (Use group D) | 10 A  |

## Approvals

Approvals institutes



## Downloads

CAD Library (P-CAD Format - Standard) SL-SMT.LIB

## Classifications

|            |             |
|------------|-------------|
| ETIM 2.0   | NK          |
| ETIM 3.0   | EC001284    |
| eClass 4.1 | 27-26-07-01 |
| eClass 5.0 | 27-26-07-01 |
| eClass 5.1 | 27-26-07-04 |

## Similar products

| Order No.  | Part designation              | Version                 |
|------------|-------------------------------|-------------------------|
| 1842080000 | SL-SMT3.5/2/90F 3.2SN SW BOX  | , No. of poles: 2, Box  |
| 1842090000 | SL-SMT3.5/3/90F 3.2SN SW BOX  | , No. of poles: 3, Box  |
| 1842100000 | SL-SMT3.5/4/90F 3.2SN SW BOX  | , No. of poles: 4, Box  |
| 1842110000 | SL-SMT3.5/5/90F 3.2SN SW BOX  | , No. of poles: 5, Box  |
| 1842120000 | SL-SMT3.5/6/90F 3.2SN SW BOX  | , No. of poles: 6, Box  |
| 1842130000 | SL-SMT3.5/7/90F 3.2SN SW BOX  | , No. of poles: 7, Box  |
| 1842140000 | SL-SMT3.5/8/90F 3.2SN SW BOX  | , No. of poles: 8, Box  |
| 1842150000 | SL-SMT3.5/9/90F 3.2SN SW BOX  | , No. of poles: 9, Box  |
| 1842160000 | SL-SMT3.5/10/90F 3.2SN SW BOX | , No. of poles: 10, Box |
| 1842170000 | SL-SMT3.5/11/90F 3.2SN SW BOX | , No. of poles: 11, Box |

|            |                                  |                         |
|------------|----------------------------------|-------------------------|
| 1842180000 | SL-SMT3.5/12/90F 3.2SN SW<br>BOX | , No. of poles: 12, Box |
| 1842190000 | SL-SMT3.5/13/90F 3.2SN SW<br>BOX | , No. of poles: 13, Box |
| 1842200000 | SL-SMT3.5/14/90F 3.2SN SW<br>BOX | , No. of poles: 14, Box |
| 1842210000 | SL-SMT3.5/15/90F 3.2SN SW<br>BOX | , No. of poles: 15, Box |
| 1842220000 | SL-SMT3.5/16/90F 3.2SN SW<br>BOX | , No. of poles: 16, Box |
| 1842230000 | SL-SMT3.5/17/90F 3.2SN SW<br>BOX | , No. of poles: 17, Box |
| 1842250000 | SL-SMT3.5/19/90F 3.2SN SW<br>BOX | , No. of poles: 19, Box |
| 1842260000 | SL-SMT3.5/20/90F 3.2SN SW<br>BOX | , No. of poles: 20, Box |
| 1842270000 | SL-SMT3.5/21/90F 3.2SN SW<br>BOX | , No. of poles: 21, Box |
| 1842280000 | SL-SMT3.5/22/90F 3.2SN SW<br>BOX | , No. of poles: 22, Box |
| 1842290000 | SL-SMT3.5/23/90F 3.2SN SW<br>BOX | , No. of poles: 23, Box |
| 1842300000 | SL-SMT3.5/24/90F 3.2SN SW<br>BOX | , No. of poles: 24, Box |