

0548	8975	3016	9548
0548-0-15-XX-21-XX-10-0 Solder mount in .036 min. mounting hole	8975-0-15-XX-21-XX-10-0 Solder mount in .036 min. mounting hole	3016-0-15-XX-21-XX-10-0 Solder mount in .036 min. mounting hole	9548-0-15-XX-21-XX-10-0 Solder mount in .036 min. mounting hole

8637	1407	0553/8553															
8637-0-15-XX-21-XX-10-0 Solder mount in .037 min. mounting hole	1407-0-15-XX-11-XX-10-0 Solder mount in .040 min. mounting hole	<table border="1"> <thead> <tr> <th>Basic Part Number</th> <th>Length L</th> <th>Depth N</th> </tr> </thead> <tbody> <tr> <td>0553-1</td> <td>.140</td> <td>.124</td> </tr> <tr> <td>0553-2</td> <td>.170</td> <td>.154</td> </tr> <tr> <td>0553-3</td> <td>.282</td> <td>.266</td> </tr> <tr> <td>8553-0</td> <td>.245</td> <td>.229</td> </tr> </tbody> </table>	Basic Part Number	Length L	Depth N	0553-1	.140	.124	0553-2	.170	.154	0553-3	.282	.266	8553-0	.245	.229
Basic Part Number	Length L	Depth N															
0553-1	.140	.124															
0553-2	.170	.154															
0553-3	.282	.266															
8553-0	.245	.229															
		X553-X-15-XX-X1-XX-10-0 Hex press-fit in .041 plated thru hole															

0566	0442	0554						
<table border="1"> <thead> <tr> <th>Basic Part Number</th> <th>Length L</th> </tr> </thead> <tbody> <tr> <td>0566-1</td> <td>.083</td> </tr> <tr> <td>0566-2</td> <td>.138</td> </tr> </tbody> </table>	Basic Part Number	Length L	0566-1	.083	0566-2	.138	0442-0-15-XX-11-XX-10-0 Solder mount in .040 min. mounting hole	0554-0-15-XX-21-XX-10-0 Solder mount in .040 min. mounting hole
Basic Part Number	Length L							
0566-1	.083							
0566-2	.138							

SPECIFICATIONS SHELL MATERIAL: Brass Alloy 360, 1/2 Hard CONTACT MATERIAL: Beryllium Copper Alloy 172, HT DIMENSION IN INCHES TOLERANCES ON: LENGTHS: ±.005 DIAMETERS: ±.002 ANGLES: ± 2°	ORDER CODE: XXXX - X - 15 - XX - XX - XX - 10 - 0	
	BASIC PART # → SPECIFY SHELL FINISH: 01 200μ" TIN/LEAD OVER NICKEL 15 10μ" GOLD OVER NICKEL	SPECIFY CONTACT FINISH: 02 200μ" TIN/LEAD OVER NICKEL 14 10μ" GOLD OVER NICKEL 27 30μ" GOLD OVER NICKEL
	SELECT CONTACT #11 or #21 CONTACT (DATA ON PAGE 206)	