



D


C

B




A



PC-BOARD HOLE LAYOUT
(COMPONENT SIDE OF BOARD SHOWN)



PART NUMBER REEL PACKAGING	PART NUMBER BOX PACKAGING	NUMBER OF POSITIONS	"A" MAX	"B"
0-215464-4	7-215464-4	4	8.3	3.81
0-215464-6	7-215464-6	6	10.9	6.35
0-215464-8	7-215464-8	8	13.4	8.89
1-215464-0	8-215464-0	10	15.9	11.43
1-215464-2	8-215464-2	12	18.5	13.97
1-215464-4	8-215464-4	14	21.0	16.51
1-215464-6	8-215464-6	16	24.0	19.05
1-215464-8	8-215464-8	18	26.1	21.59
2-215464-0	9-215464-0	20	28.6	24.13




SCALE 3:1

SHOWN IS A 10 POSITION
CONNECTOR (1-215464-0).


THIS DRAWING IS A CONTROLLED DOCUMENT.	
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: ±0.20
	0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ± FINISH
MATERIAL SEE TABLE	SEE TABLE

LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN
H	-		R	CONTACT MATERIAL CHANGED TO PHOSPHOR BRONZE	13APR2018	SS



SCALE 3:10

BOX PACKAGING
250 PARTNUMBERS PER BOX
FOR ALL PARTNUMBERS.



REEL PACKAGING
DEREELING DIRECTION AND CONNECTOR POSITION
2500 CONNECTORS PER REEL FOR ALL PART NUMBERS

2	MALE CONTACT	PHOSPHOR BRONZE	3-5 µm Sn over 0.5 µm min Ni
1	HOUSING	G.F. POLYESTER, PBT	RED
ITEM NO.	DESCRIPTION	MATERIAL	FINISH / COLOR
DWN	15-04-1992	TE Connectivity	
CHK	J. VAN DREUMEL		
APVD	H. KOKKEN	NAME Micro-MaTch MALE-ON-BOARD LONG POST, POLARIZED	
PRODUCT SPEC	108-19052		
APPLICATION SPEC	-	SIZE	CAGE CODE
WEIGHT	-	DRAWING NO	RESTRICTED TO
CUSTOMER DRAWING		A200779	C-215464
SCALE 8:1		SHEET 1 OF 1	REV R