



780-518 "Marshal Bean" Protective Rubber Cover Universal D-Subminiature for MIL-DTL-24308 Connectors



*"To Protect
and to Serve"*

780-518-15P G 12 - 03 C

Product Series _____
Basic Number _____
Shell Size (Table I) _____
Attachment Rope _____
Attachment Length in Inches
($\pm .250$ (6.35) Inch)

C = Conductive
(Omit for Standard)

Attachment Type (Table II)

G = Nylon Rope
(Omit for None)




TABLE I: SHELL SIZE & COVER DIMENSIONS

Shell Size	A	B	C	D
09S	.610 (15.5)	.280 (7.1)	.220 (5.6)	.820 (20.8)
09P	.650 (16.5)	.330 (8.4)	.230 (5.8)	.820 (20.8)
15S	.940 (23.9)	.280 (7.1)	.240 (6.1)	1.260 (32.0)
15P	.970 (24.6)	.330 (8.4)	.240 (6.1)	1.260 (32.0)
25S	1.480 (37.6)	.280 (7.1)	.250 (6.4)	1.760 (44.7)
25P	1.500 (38.1)	.330 (8.4)	.250 (6.4)	1.780 (45.2)
37S	2.120 (53.8)	.280 (7.1)	.230 (5.8)	2.290 (58.2)
37P	2.150 (54.6)	.330 (8.4)	.230 (5.8)	2.290 (58.2)
50S	2.030 (51.6)	.390 (9.9)	.240 (6.1)	2.170 (55.1)
50P	2.050 (52.0)	.450 (11.4)	.230 (5.8)	2.230 (56.6)

**TABLE II:
ATTACHMENT
TYPE**

Dash No.	E Dia $\pm .010$ (0.3)
00	No Terminal
01	.140 (3.6)
02	.182 (4.6)
03	.191 (4.9)
04	.197 (5.0)
05	.167 (4.2)
06	.125 (3.2)
07	.218 (5.5)
09	.156 (4.0)
WS	With Strap
SK	Slip Knot

NOTES:

- Cover Identified in area shown.
- Metric dimensions (mm) are indicated in parentheses.
- This series of covers is similar to Bean Rubber Mfg. Co. BP-D Subminiature Series, same Dash No.,
i.e.: BP-DAM15P-WS-L6 equivalent to 780-518-15PG6-WS
- Standard material contains trace amounts of sulfur (a vulcanizing agent) which is known to contribute to degradation/corrosion of silver plated components such as braid, etc. Specify MOD Code suffix -675 for sulfur-free material.