



Mini-Com® Executive Series Faceplates

- Accept Mini-Com® Modules for STP and UTP, fiber optic, and audio/video, which snap in and out for easy moves, adds, and changes
- Include label/label covers for easy port identification
- Raised rail design for aesthetic appeal



CFPE1IWY CFPE2IWY CFPE4IWY



CFPE6IWY CFPE10IW-2GY

Part Number	Part Description	Color‡	Std. Pkg. Qty.	Std. Ctn. Qty.
CFPE1IWY	Single gang, vertical faceplate accepts one Mini-Com® Module.	Off White	1	10
CFPE2IWY	Single gang, vertical faceplate accepts two Mini-Com® Modules.	Off White	1	10
CFPE4IWY	Single gang, vertical faceplate accepts four Mini-Com® Modules.	Off White	1	10
CFPE6IWY	Single gang, vertical faceplate accepts six Mini-Com® Modules. Requires minimum 1.9" wide electrical box for proper mounting.	Off White	1	10
CFPE10IW-2GY	Double gang, vertical faceplate accepts ten Mini-Com® Modules.	Off White	1	10

‡For other colors replace suffix IW (Off White) with EI (Electric Ivory), WH (White), or IG (International Gray). All faceplates supplied with mounting screws.

Component Labels for Mini-Com® Executive Series Faceplates



Suggested Label Solutions for TIA/EIA-606-A Compliance				
Faceplate Part Number	Laser/Ink Jet Desktop Printer Label	TDP43ME Thermal Transfer Desktop Printer Label	PanTher™ LS8E Hand-Held Printer Label	Cougar™ LS9 Hand-Held Printer Label
CFPE1**Y	C195X040Y1J	C195X040Y1T	C195X040Y1C	T038X000FJC-BK‡
CFPE2**Y				
CFPE4**Y				
CFPE6**Y				
CFPE10**-2GY	C288X040Y1J	C288X040Y1T	C288X040Y1C	T038X000FJC-BK‡

For complete labeling solutions and product information, reference charts on pages O.1 – O.22 of SA-NCCB51.

‡For non-adhesive labeling solution, do not remove liner from label.



Mini-Com® Sloped Executive Series Faceplate Kit

- Accepts Mini-Com® Modules for STP and UTP, fiber optic, and audio/video, which snap in and out for easy moves, adds, and changes
- Sloped inserts are front releasable
- Includes label/label covers for easy port identification
- Raised rail design for aesthetic appeal



Part Number	Part Description	Color‡	Std. Pkg. Qty.	Std. Ctn. Qty.
CFPSE4IWY	Single gang, vertical faceplate frame and two sloped inserts (two module spaces each). Accepts four Mini-Com® Modules.	Off White	1	10

‡For other colors replace suffix IW (Off White) with EI (Electric Ivory), WH (White), or IG (International Gray). All faceplates supplied with mounting screws.