

P	LTR	DESCRIPTION	DATE	OWN	APVD
0		PRELIMINARY ISSUE	03MAY2001	M.B.	O.C.
A		FIRST ISSUE (ET00-0117-02)	21JUN2002	M.B.	O.C.
B		MODIFIED SHELL SLOT SHAPE AND RELEASED FOR PRODUCTION (ET00-0099-04)	20JUL2004		

NOTES
(NOTE)

1) SLOT SUITABLE FOR HOUSING P/N 284224-2
(CAVITA' ADATTA PER L'HOUSING P/N 284224-2)

2) THE PRODUCT IS SUPPLIED WITH LEVER IN CLOSED POSITION
(IL PRODOTTO VIENE FORNITO CON LA LEVA IN POSIZIONE CHIUSA)


3) PRODUCT SUITABLE FOR PIN HEADER 24+24 POSITIONS
CODE TYPE A, P/N 953621-... OR PIN HEADER 24+32
POSITIONS KEY GEOMETRY AA_Aa, P/N 1355737-...
(IL PRODOTTO E' ADATTO PER IL PIN HEADER 24+24
POSITION CODE TYPE A, P/N 953621-... O PER IL PIN)
HEADER 24+32 POSITION KEY GEOMETRY AA_Aa,
P/N 1355737-...)

4) FOR PROPER MATING WITH PIN HEADER 24+24 POSITION
SEE INSTRUCTION SHEET N. 411-20054
(PER UN CORRETTO ACCOPPIAMENTO CON IL PIN HEADER
24+24 POSITION VEDERE FOGLIO ISTRUZIONI
N. 411-20054)



ITEM (VOCE)	DESCRIPTION (DESCRIZIONE)	MATERIAL (MATERIALE)	Q.TY (Q.TA')
1	LEVER (LEVA)	PA 66 GF COLOR GREEN (COLORE VERDE)	1
2	SHELL (CORAZZA)	PA 66 GF COLOR BLACK (COLORE NERO)	1

284714-2 AS SHOWN
(COME MOSTRATO)

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN M. BARBERIS 03MAY2001	tyco Electronics AMP Italia S.p.A. C.so F.lli Cervi, 15 Collegno (TO)	
DIMENSIONS: mm		CHK O. CANUTO 03MAY2001	NAME	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD A. GENTA	24 POSITIONS AIRBAG SHELL WITH LEVER ASS'Y (CODE A)	
0 PLC ±0.3 1 PLC ±0.2 2 PLC ±0.2 3 PLC ± 4 PLC ± ANGLES ±1°		PRODUCT SPEC 108-20202	SIZE CAGE CODE DRAWING NO	
MATERIAL SEE TABLE (VEDI TABELLA)		APPLICATION SPEC 114-15077	A3 00779 C-284714	
FINISH SEE TABLE (VEDI TABELLA)		WEIGHT -	RESTRICTED TO -	
CUSTOMER DRAWING		SCALE 2:1	SHEET 1 OF 4 REV B	



SEE SHEET 1 (VEDI FOGLIO 1)




ITEM (VOCE)	DESCRIPTION (DESCRIZIONE)	MATERIAL (MATERIALE)	Q.TY (Q.TA')
1	LEVER (LEVA)	PA 66 GF COLOR GREEN (COLORE VERDE)	1
2	SHELL (CORAZZA)	PA 66 GF COLOR GRAY (COLORE GRIGIO)	1

NOTES
(NOTE)

1 SLOTT SUITABLE FOR HOUSING P/N 284224-1
(CAVITA' ADATTA PER L'HOUSING P/N 284224-1)

2) FOR MISSING NOTES AND DIMENSIONS SEE
P/N 284714-2, SHEET 1 OF 4
(PER LE NOTE E LE QUOTE MANCANTI VEDERE
P/N 284714-2, FOGLIO 1 DI 4)

3) PRODUCT SUITABLE FOR PIN HEADER 24+24 POSITIONS
CODE TYPE B, P/N 953621-... OR PIN HEADER 24+32
POSITIONS KEY GEOMETRY AB_Ab, P/N 1355737-...
(IL PRODOTTO E' ADATTO PER IL PIN HEADER 24+24
POSITION CODE TYPE B, P/N 953621-... O PER IL PIN
HEADER 24+32 POSITION KEY GEOMETRY AB_Ab,
P/N 1355737-...)



284714-1 AS SHOWN
(COME MOSTRATO)

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION
IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.

DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:
	0 PLC ±0.3 1 PLC ±0.2 2 PLC ±0.2 3 PLC ± 4 PLC ± ANGLES ±°
MATERIAL SEE TABLE (VEDI TABELLA)	FINISH SEE TABLE (VEDI TABELLA)

DWN M. BARBERIS	03MAY2001
CHK O. CANUTO	03MAY2001
APVD A. GENTA	-
PRODUCT SPEC	108-20202
APPLICATION SPEC	114-15077
WEIGHT	-
CUSTOMER DRAWING	

tyco
Electronicstyco Electronics AMP Italia S.p.A.
C.so F.lli Cervi, 15 Collegno (TO)

NAME	24 POSITIONS AIRBAG SHELL WITH LEVER ASS.Y (CODE B)
SIZE	A3
CAGE CODE	00779
DRAWING NO	C-284714
RESTRICTED TO	-
SCALE	2:1
SHEET	2
OF	4
REV	B

SEE SHEET 1 (VEDI FOGLIO 1)

ITEM (VOCE)	DESCRIPTION (DESCRIZIONE)	MATERIAL (MATERIALE)	Q.TY (Q.TA')
1	LEVER (LEVA)	PA 66 GF COLOR GREEN (COLORE VERDE)	1
2	SHELL (CORAZZA)	PA 66 GF COLOR BROWN (COLORE MARRONE)	1

NOTES
(NOTE)

1 SLOT SUITABLE FOR HOUSING P/N 284224-5
(CAVITA' ADATTA PER L'HOUSING P/N 284224-5)

2) FOR MISSING NOTES AND DIMENSIONS SEE
P/N 284714-2, SHEET 1 OF 4
(PER LE NOTE E LE QUOTE MANCANTI VEDERE
P/N 284714-2, FOGLIO 1 DI 4)

3) PRODUCT SUITABLE FOR PIN HEADER 24+24 POSITIONS
CODE TYPE C, P/N 953621-...
(IL PRODOTTO E' ADATTO PER IL PIN HEADER 24+24
POSITION CODE TYPE C, P/N 953621-...)

284714-3 AS SHOWN
(COME MOSTRATO)

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION
IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.

DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:	
		0 PLC	±0.3
		1 PLC	±0.2
		2 PLC	±0.2
		3 PLC	±
		4 PLC	±
		ANGLES	±1°
MATERIAL	SEE TABLE (VEDI TABELLA)	FINISH	SEE TABLE (VEDI TABELLA)

DWN	M. BARBERIS	03MAY2001
CHK	O. CANUTO	03MAY2001
APVD	A. GENTA	-
PRODUCT SPEC	108-20202	
APPLICATION SPEC	114-15077	
WEIGHT	-	
CUSTOMER DRAWING		

tyco Electronics		tyco Electronics AMP Italia S.p.A. C.sp F.lli Cervi, 15 Collegno (TO)	
NAME		24 POSITIONS AIRBAG SHELL WITH LEVER ASS'Y (CODE C)	
SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C-284714	-
SCALE		SHEET	OF
2:1		3	4
		REV	B

P	LTR	DESCRIPTION	DATE	DWN	APVD
		SEE SHEET 1 (VEDI FOGLIO 1)			

ITEM (VOCE)	DESCRIPTION (DESCRIZIONE)	MATERIAL (MATERIALE)	Q.TY (Q.TA')
1	LEVER (LEVA)	PA 66 GF COLOR GREEN (COLORE VERDE)	1
2	SHELL (CORAZZA)	PA 66 GF COLOR BLUE (COLORE BLU)	1

NOTES
(NOTE)

1) SLOT SUITABLE FOR HOUSING P/N 284224-6
(CAVITA' ADATTA PER L'HOUSING P/N 284224-6)

2) FOR MISSING NOTES AND DIMENSIONS SEE DRAWING
P/N 284714-2, SHEET 1 OF 4
(PER LE NOTE E LE QUOTE MANCANTI VEDERE DISEGNO
P/N 284714-2, FOGLIO 1 DI 4)

3) PRODUCT SUITABLE FOR PIN HEADER 24+24 POSITIONS
CODE TYPE D, P/N 953621-... OR PIN HEADER 24+32
POSITIONS KEY GEOMETRY AD_Ad, P/N 1355737-...
(IL PRODOTTO E' ADATTO PER IL PIN HEADER 24+24
POSITION CODE TYPE D, P/N 953621-... O PER IL PIN
HEADER 24+32 POSITION KEY GEOMETRY AD_Ad,
P/N 1355737-...)

284714-4 AS SHOWN
(COME MOSTRATO)

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION
IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.

DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:
mm	
	0 PLC ±0.3 1 PLC ±0.2 2 PLC ±0.2 3 PLC ± 4 PLC ± ANGLES ±1°
MATERIAL SEE TABLE (VEDI TABELLA)	FINISH SEE TABLE (VEDI TABELLA)

DWN	M. BARBERIS	03MAY2001
CHK	O. CANUTO	03MAY2001
APVD	A. GENTA	
PRODUCT SPEC	108-20202	
APPLICATION SPEC	114-15077	
WEIGHT	-	
CUSTOMER DRAWING		

tyco
Electronics

tyco Electronics AMP Italia S.p.A.
C.so F.lli Cervi, 15 Collegno (TO)

NAME	24 POSITIONS AIRBAG SHELL WITH LEVER ASS'Y (CODE D)	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
		A3	00779	C=284714	-
SCALE	2:1	SHEET	4	OF	4
REV	B				