

SMA CONNECTORS



TE CONNECTIVITY (TE)

2037 8126 92

AMP | SM , SMA

1052203-1

TE Internal Number: 1052203-1

Mil-Spec: M39012/56-3126

Alias ID: 2037-8126-92

Always EU RoHS/ELV Compliant

Applies To **Coaxial Cable**

Panel Mount **Without**

Body Material **Stainless Steel**

Body Plating Finish **Passivated**

50 Ohm **Yes**

✓ Active

 **PRODUCT DRAWING**
English

 **3D PDF**

Product Drawings

SMA RIGHT ANGLE CABLE PLUG-CRIMP ATTACHMENT (M39012/56-3126) CAT C

PDF **(TIFF AVAILABLE)**
English

SMA RIGHT ANGLE CABLE PLUG-CRIMP ATTACHMENT (M39012/56-3126) CAT C

PDF **(TIFF AVAILABLE)**
English

CAD Files

Customer View Model

2D_DXF.ZIP
English

3D PDF
PDF
3D

Customer View Model

3D_IGS.ZIP
English

Customer View Model

3D_STP.ZIP
English

Instruction Sheets

Instruction Sheet (U.S.)

SMA Right-Angle Cable Plugs

PDF
English

Please review product documents or [contact us](#) for the latest agency approval information. Please Note: Use the Product Drawing for all design activity.

Product Type Features

Applies To

Coaxial Cable

RF Connector Type

SMA

Connector Style	Plug
Cable Type	RG 174, RG 188, RG 188A, RG 316
Product Type	Connector - RF
Shrink Tubing	Without
Retractable Collar	Without
Dielectric Material	PTFE Fluorocarbon
<hr/>	
Configuration Features	Snap-Lock
	Without
<hr/>	
Electrical Characteristics	50 Ohm
	Yes
	75 Ohm
	No
<hr/>	
Signal Characteristics	Frequency (GHz)
	12.4
<hr/>	
Body Features	Body Material
	Stainless Steel
	Body Plating Finish
	Passivated
	Body Style
	Right Angle
	Gasket Material
	Silicone Rubber
	Ferrule Material
	Brass, Copper
<hr/>	
Contact Features	Center Contact Plating Material
	Gold
	Center Contact
	With
	Center Contact Material
	Brass
	Captivated Contacts
	With
<hr/>	
Termination Features	Cable Termination Type
	Crimp
<hr/>	
Mechanical Attachment	Panel Mount
	Without
	Safety Wire Holes
	Without
	Coupling Nut Material
	Stainless Steel
<hr/>	
Dimensions	Length
	34.93 mm [1.375 in]
<hr/>	
Industry Standards	Military Category
	C
<hr/>	
Packaging Features	Packaging Method
	Package
<hr/>	

Product Compliance

[Statement of Compliance](#)
PDF

[VIEW ALL PRODUCT COMPLIANCE](#)