

## HC-5 Product Details

**HC-5**

(5-1618274-5)

TE Internal Number: 5-1618274-5



### High Voltage Relays

[Not EU RoHS or ELV Compliant](#)**Product Highlights:**

- Contact Arrangement = 1 Form B, SPST-NC, 1 N/C, 1 Form A, SPST-NO, 1 N/O, 1 Form C, SPDT, 1 C/O
- Power Switching = Make Only, No
- Contact Current Rating = 0 - 8 Amps.
- Not RF Rated
- Coil Voltage = 26.5 VDC

[View all Features](#)**Quick Links**[Check Pricing & Availability](#)[Search for Tooling](#)[Product Feature Selector](#)[Contact Us About This Product](#)[Add to My Part List](#)[Request Sample](#)[Find Similar Products](#)[Buy Product](#)

### Documentation & Additional Information

**Product Drawings:**

- None Available

**Catalog Pages/Data Sheets:**

- None Available

**Product Specifications:**

- None Available

**Application Specifications:**

- None Available

**Instruction Sheets:**

- None Available

**CAD Files:**

- None Available

**Additional Information:**

- [Product Line Information](#)

**Related Products:**

- [Tooling](#)

### Product Features (Please use the Product Drawing for all design activity)

**Product Type Features:**

- [Termination Style](#) = Turret Terminal

**Electrical Characteristics:**

- [Contact Current Rating \(Amps.\)](#) = 0 - 8
- [RF Rated](#) = No
- [Coil Voltage \(VDC\)](#) = 26.5
- [Voltage, Max. \(VDC\)](#) = 0 - 3500
- Current, Carry Only = Yes

**Termination Related Features:**

- [High Voltage Connection \(Power\)](#) = Bifurcated Terminals
- [High Voltage Connection \(Coil\)](#) = Turret Terminals
- [Auxiliary Contacts](#) = Without

**Body Related Features:**

- [Mount Style](#) = Non-Flanged

**Configuration Related Features:**

- [Contact Arrangement](#) = 1 Form B, SPST-NC, 1 N/C, 1 Form A, SPST-NO, 1 N/O, 1 Form C, SPDT, 1 C/O
- [Power Switching](#) = Make Only, No
- [Economizer](#) = Without

**Industry Standards:**

- [RoHS/ELV Compliance](#) = Not ELV/RoHS compliant
- [Lead Free Solder Processes](#) = Not suitable for lead free processing

**Other:**

- Brand = Kilovac

**Corporate Information**[Who We Are](#)[Investors](#)[News Room](#)[Supplier Portal](#)[Careers](#)**Quick Links**[Check Distributor Inventory](#)[Cross Reference](#)[Find Documents & Drawings](#)[Product Compliance Support Center](#)[Site Map](#)**Customer Support**[Email or Chat with Us](#)[Find a Phone Number](#)[Search Knowledge Base](#)[Manage Your Account](#)