

IE-PS-V04P-2SC-POF-BP**Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com



PushPull plug-in connector set according to IEC
61076-3-106 ver.4 (IEC24702), plastic with SC insert

General ordering data

Version	FO connector, Version 4, SC-RJ POF, kink prevention, IP67
Order No.	1963390000
Type	IE-PS-V04P-2SC-POF-BP
GTIN (EAN)	4032248651863
Qty.	10 pc(s).

IE-PS-V04P-2SC-POF-BP

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

Technical data

Dimensions and weights

Depth	129.8 mm	Depth (inches)	5.11 inch
Height	20.1 mm	Height (inches)	0.791 inch
Width	20.2 mm	Width (inches)	0.795 inch
Net weight	54.3 g		

Temperatures

Operating temperature -40 °C...70 °C

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1, 6,6'-di-tert-butyl-2,2'-methylenedi-p-cresol 119-47-1	SCIP	e5bbf197-73b5-420b-90c0-0173b7b
------------	---	------	---------------------------------

General data

Colour	Miscellaneous	Connection 1	SCRJ
Connection 2	Rapid connection system: crimping, cutting	Description of article	Version 4, SC-RJ POF, kink prevention
Fibre type	POF	Housing main material	PA UL 94 V0
Housing material, insert	PA, Zinc diecast	Insertion loss	0.5 dB singlemode, 0.4 dB multimode, ≤ 1.0 dB POF
Plugging cycles	500	Protection degree	IP67
Return loss (attenuation)	40 dB singlemode; 30 dB multimode	Sheath diameter, max.	10 mm
Sheath diameter, min.	5 mm		

General standards

Connector standard IEC 61076-3-106 Var. 4, IEC 61754-24

Classifications

ETIM 6.0	EC001122	ETIM 7.0	EC001122
ETIM 8.0	EC001122	ECLASS 9.0	19-17-01-22
ECLASS 9.1	19-17-01-22	ECLASS 10.0	19-17-01-22
ECLASS 11.0	19-17-01-22	ECLASS 12.0	19-17-01-22

Approvals

Approvals



ROHS

Conform

IE-PS-V04P-2SC-POF-BP

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

Technical data

info@weidmueller.com

www.weidmueller.com

Downloads

Approval/Certificate/Document of
Conformity

[GOST Approval](#)

Engineering Data

[WSCAD](#)

Product Change Notification

[20210412 Technical change for cap nut V1 and V4](#)

[20210412 Technische Änderung zu Hutmutter V1 und V4](#)

User Documentation

[MAN IE GUIDE DE](#)

[MAN IE GUIDE EN](#)

[Designation key / Type key](#)

Catalogues

[Catalogues in PDF-format](#)

Brochures

[FL FIELDWIRING EN](#)

[PI PROFINET CABLING EN](#)

IE-PS-V04P-2SC-POF-BP

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

Drawings

Dimensioned drawing

