

IE-BI-LCD-MM-C**Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com



FO LC inserts for plug-in connectors ver.1 / 4 / 14

General ordering data

Version	LC insert, Bulkhead insert LC duplex, multimode
Order No.	1964420000
Type	IE-BI-LCD-MM-C
GTIN (EAN)	4032248649037
Qty.	10 pc(s).

IE-BI-LCD-MM-C

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

Technical data

Dimensions and weights

Depth	30 mm	Depth (inches)	1.181 inch
Height	13.2 mm	Height (inches)	0.52 inch
Width	15.6 mm	Width (inches)	0.614 inch
Net weight	13.6 g		

Temperatures

Operating temperature	-40 °C...70 °C	Humidity	0...85 % rel. humidity
-----------------------	----------------	----------	------------------------

General data

Colour	Miscellaneous	Configuration	Connector and flange insert for variant 1, 4 and 14 housings
Connection 1	LC Duplex	Connection 2	LC Duplex
Description of article	Bulkhead insert LC duplex, multimode	Fibre type	Multimode
Housing main material	PBT diecast zinc	Humidity	0...85 % rel. humidity
Insertion loss	≤ 0.4 dB	Plugging cycles	1000
Protection degree	IP67 with housing	Return loss (attenuation)	≥ 30 dB

General standards

Connector standard	IEC 61754-20
--------------------	--------------

Classifications

ETIM 6.0	EC001122	ETIM 7.0	EC001122
ETIM 8.0	EC001122	ECLASS 9.0	19-17-01-22
ECLASS 9.1	19-17-01-22	ECLASS 10.0	19-17-01-22
ECLASS 11.0	19-17-01-22	ECLASS 12.0	19-17-01-22

Approvals

ROHS	Conform
------	---------

Downloads

Approval/Certificate/Document of Conformity	GOST Approval
Engineering Data	CAD data – STEP
User Documentation	MAN IE GUIDE DE MAN IE GUIDE EN Designation key / Type key
Catalogues	Catalogues in PDF-format
Brochures	FL FIELDWIRING EN PI PROFINET CABLING EN PI PROFINET CABLING EN

IE-BI-LCD-MM-C

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

Drawings

Dimensioned drawing

