

USB-C to USB-A Adapter (F/M), USB 3.2 Gen 1 (5 Gbps)

MODEL NUMBER: U329-000



Connects a USB-C device to the USB-A port on your computer, laptop or USB hub.

Features

Connects a USB-C Device to Your Computer or Laptop's USB-A Port

The U329-000 lets you connect a device with USB-C capabilities, such as a smartphone, tablet or hard drive, to the USB-A port on your PC, laptop or USB hub. The palm-sized adapter fits to the end of a USB-C cable, giving you maximum flexibility and more opportunities to share data or charge your phone using a USB-A laptop or wall charger. **Note:** This adapter does not support video.

Transfers Data at Fast USB 3.2 Gen 1 Speeds

This USB adapter supports USB 3.2 Gen 1 data transfer speeds up to 5 Gbps, which is 10 times faster than USB 2.0. It also produces up to 0.9A for charging and powering mobile devices. The U329-000 is backward compatible with previous USB generations, so you can continue using older devices while getting high-speed performance from new devices.

Ready to Use Right Out of the Package

The plug-and-play USB 3.2 Gen 1 adapter is specifically designed to accept USB-C and Thunderbolt 3 plugs from a wide variety of cables, hubs, hard drives, adapters and other compatible devices. It requires no software or external power. It is small enough to carry in your pocket, purse, briefcase or laptop bag, so you'll always be ready to connect wherever you are.

Specifications

OVERVIEW	
UPC Code	037332213976
Technology	USB 3.x
INPUT	
Bus Powered	Yes
POWER	

Highlights

- Converts a male USB-C connector to a male USB-A connector
- Supports USB 3.2 Gen 1 speeds up to 5 Gbps to ensure fast data transfers
- Produces 900mA (0.9A) for charging and powering phones and other mobile devices
- Backwards compatible with previous USB generations
- Plug-and-play operation with no software required for easy, immediate installation

System Requirements

- Device with USB-A port
- Device with USB-C port
- USB-C cable (M/M)

Package Includes

U329-000 USB-C to USB-A Adapter (F/M)



Powering Business Worldwide



USB Power Delivery (PD) Charging Support	No
CONNECTIONS	
Number of Ports	1
Side A - Connector 1	USB A (MALE)
Side B - Connector 1	USB C (FEMALE)
Connector Plating	Nickel
Contact Plating	Gold
CHARGING	
Total Charging Amps	0.9
Charging Ports / Amps	0.9A
PHYSICAL	
Color	Black
Material of Construction	PVC, UL94V-0
Shipping Dimensions (hwd / in.)	5.90 x 3.90 x 0.50
Shipping Dimensions (hwd / cm)	14.99 x 9.91 x 1.27
Shipping Weight (lbs.)	0.02
Unit Dimensions (hwd / in.)	0.310 x 0.630 x 1.100
Unit Dimensions (hwd / cm)	0.79 x 1.6 x 2.79
Unit Packaging Type	Polybag
Unit Weight (lbs.)	0.01
Unit Weight (kg)	0.00
ENVIRONMENTAL	
Operating Temperature Range	32° to 113°F (0° to 45°C)
Storage Temperature Range	14° to 158°F (-10° to 70°C)
Operating Humidity Range	10% to 85% RH, Non-Condensing
Storage Humidity Range	5% to 90% RH, Non-Condensing
Power Provided to Connected Device(s)	5V, 0.9A
FEATURES & SPECIFICATIONS	
USB Specification	USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps); USB 3.2 Gen 1 (up to 5 Gbps)
Driver Required	No
STANDARDS & COMPLIANCE	

Product Certifications	EN 55024; EN 55032
Product Compliance	RoHS; CE (Europe); REACH; FCC (USA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.