

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

50-36-1666

Status:

Active

Overview:

Mini-Fit Jr.™

Description:

4.20mm Pitch Mini-Fit Jr.™ Receptacle Housing, Single Row, PA Polyamide Nylon 6/6, UL 94V-0, 5 Circuits, Passive Latch, Glow Wire Compatible



Series

image - Reference only

Documents:

- [3D Model](#)
- [Drawing \(PDF\)](#)
- [Product Specification PS-5556-001 \(PDF\)](#)
- [Packaging Specification PK-5557-003 \(PDF\)](#)
- [Test Summary TS-5556-002 \(PDF\)](#)
- [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA

UL

LR19980

E29179

General

Product Family

Series

Application

Comments

Crimp Housings

5557

Power, Wire-to-Wire

Current = 13A max. per circuit when header is mated to a receptacle loaded with 45750 series terminals crimped to 16 AWG wire. . See Molex product specification PS-45750-001 for additional current derating information.

Overview

Product Name

Mini-Fit Jr.™

Mini-Fit Jr.™

Physical

Breakaway

Circuits (maximum)

Color - Resin

Flammability

Gender

Glow-Wire Compliant

Keying to Mating Part

Lock to Mating Part

Material - Resin

Number of Rows

Packaging Type

Panel Mount

Pitch - Mating Interface

Pitch - Termination Interface

Polarized to Mating Part

Ports

Stackable

Temperature Range - Operating

No

5

Black

94V-0

Receptacle

Yes

None

Yes

Nylon

1

Bag

No

4.20mm

4.20mm

Yes

1

No

-40°C to +105°C

Electrical

Current - Maximum per Contact

13A

Material Info

Old Part Number

5557-05R4-225

Reference - Drawing Numbers

Packaging Specification

Product Specification

Sales Drawing

PK-5557-003

PS-5556-001

SD-5557-525

EU RoHS

ELV and RoHS
Compliant
REACH SVHC
Contains SVHC: No
Low-Halogen Status
Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

5557Series

Mates With

5559 Crimp Housings Plug,

Use With

5556 Female Terminal Mini-Fit® Crimp Terminal

This document was generated on 04/16/2012

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION