




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A1	REVISED PER ECN-23-230183	07SEP2023	DW	JH




- NOTE : UNLESS OTHERWISE SPECIFIED
- FABRICATE TO MEET IPC – 6012, CLASS 2.
INSPECT TO MEET IPC – A – 600, CLASS 2.
 - MATERIALS
 - 2-1. ANTENNA : INJECTION MOLD AND STAMPING
 - 2-2. EVB MATERIAL : FR4 PCB, OVERALL THICKNESS 1.00mm
 - 2-3. SMA(FEMALE) PANEL TYPE CONN. : 50 OHMS(IMPEDANCE)
 - 2-4. MEASURED WITH MATCHING CIRCUIT CONDITIONS.
 - GENERAL TOLERANCES : ± 0.20
 - PACKAGING : SEE SHEET2
 - CONSULT TE CONNECTIVITY DATA SHEET DS1513634.
 - SILKSCREEN : WITHE EPOXY INK.
 - A: TE LOGO, TE P/N
 - B: WORD REV., FOLLOWED BY THE LASTEST REVISION LETTER. AS SHOWN.
 - C: 4 DIGITS DATE CODE: FIRST 2 DIGITS FOR THE WEEK CODE AND THE 2 DIGITS FOR THE YEAR CODE.
 - OTHERS: SPECIFIC TE INTERNAL USE ONLY.




THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN DW.PARK 16AUG2022		TE Connectivity				
		CHK H.SHIN 16AUG2022						
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME 1513634-1 ANTENNA WITH EVB ASSY				
		APVD CY.PARK 16AUG2022						
		PRODUCT SPEC —						
		APPLICATION SPEC —						
		WEIGHT —						
MATERIAL —		FINISH —		SIZE A3	CAGE CODE 00779	DRAWING NO C-8-1513634	RESTRICTED TO —	
CUSTOMER DRAWING						SCALE 1:1	SHEET 1 OF 2	REV A1


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-



8-1513634-1




INDIVIDUAL BOX




1 PC/1 Individual Box

Induvidual box Label



40 PCS Individual Box / 1 Carton Box



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN DW.PARK	16AUG2022	TE Connectivity		
		CHK H.SHIN	16AUG2022			
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD CY.PARK	16AUG2022	NAME 1513634-1 ANTENNA WITH EVB ASSY		
		PRODUCT SPEC				
	0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -	APPLICATION SPEC		SIZE	CAGE CODE	DRAWING NO
		WEIGHT	-	A3	00779	C-8-1513634
MATERIAL	FINISH	CUSTOMER DRAWING		SCALE	SHEET	REV
-	-			1:1	2 OF 2	A1