

**ZVR ZP2.5****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Product image**

The plugs can be securely and easily fixed to the base terminal by using a locking element. The locking element avoids an unintentional disconnection of the plugs from the base terminal and ensures maximum safety.

**General ordering data**

|            |                                         |
|------------|-----------------------------------------|
| Version    | Z-series, Locking clips, yellow, 3.9 mm |
| Order No.  | <a href="#">1816130000</a>              |
| Type       | ZVR ZP2.5                               |
| GTIN (EAN) | 4032248370702                           |
| Qty.       | 25 pc(s).                               |

**ZVR ZP2.5****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data****Dimensions and weights**

|            |          |                 |            |
|------------|----------|-----------------|------------|
| Depth      | 8.46 mm  | Depth (inches)  | 0.333 inch |
| Height     | 31.35 mm | Height (inches) | 1.234 inch |
| Width      | 3.9 mm   | Width (inches)  | 0.154 inch |
| Net weight | 0.352 g  |                 |            |

**Temperatures**

|                                  |                |                                  |     |
|----------------------------------|----------------|----------------------------------|-----|
| Storage temperature              | -25 °C...55 °C | Continuous operating temp., min. | -50 |
| Continuous operating temp., max. | 100            |                                  |     |

**Material data**

|                           |             |        |        |
|---------------------------|-------------|--------|--------|
| Material                  | PA 66 GF 30 | Colour | yellow |
| UL 94 flammability rating | HB          |        |        |

**System specifications**

|         |         |
|---------|---------|
| Version | Latches |
|---------|---------|

**Additional technical data**

|                     |                 |
|---------------------|-----------------|
| Installation advice | Direct mounting |
|---------------------|-----------------|

**General**

|                     |                 |
|---------------------|-----------------|
| Installation advice | Direct mounting |
|---------------------|-----------------|

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC002848    | ETIM 7.0    | EC002848    |
| ETIM 8.0    | EC002848    | ECLASS 9.0  | 27-14-11-92 |
| ECLASS 9.1  | 27-14-11-92 | ECLASS 10.0 | 27-14-11-92 |
| ECLASS 11.0 | 27-14-11-92 | ECLASS 12.0 | 27-14-11-92 |

**Approvals**

Approvals



|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

**Downloads**

|                                             |                                                 |
|---------------------------------------------|-------------------------------------------------|
| Approval/Certificate/Document of Conformity | <a href="#">DNVGL certificate</a>               |
| Engineering Data                            | <a href="#">CAD data – STEP</a>                 |
| Engineering Data                            | <a href="#">EPLAN, WSCAD, Zuken E3.S</a>        |
| User Documentation                          | <a href="#">StorageConditionsTerminalBlocks</a> |
| Catalogues                                  | <a href="#">Catalogues in PDF-format</a>        |
| Brochures                                   |                                                 |

### ZVR ZP2.5

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings

