


Product data sheet

Characteristics

SQWP141002BK

Cover frame, X Series, 2 gangs, screwless, black, matte finish



Main

Range	Square D X Series
Product or Component Type	Cover frame
Accessory / separate part category	Installation accessory
Aesthetic name	X Series
Number of gangs	2 gangs
Product destination	Switch Dimmer Socket-outlet Sensor Fan controller USB charger + socket-outlet
Color	Black

Complementary

Suitable for body type	Decorator
Fixing Mode	Screwless
Material	Plastic
Surface treatment	Painted
Surface Finish	Matte
Height	4.72 in (120 mm)
Width	4.57 in (116 mm)
Depth	0.28 in (7 mm)
Quantity per Set	1 piece

Environment

Product Certifications	cULus
Standards	UL 514D

Ordering and shipping details

Category	09936-WD AESTHETIC WALL PLATES
Discount Schedule	DE9
GTIN	785901551133
Returnability	Yes
Country of origin	CN

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.28 in (0.7 cm)
Package 1 Width	4.57 in (11.6 cm)
Package 1 Length	4.72 in (12.0 cm)
Package 1 Weight	1.69 oz (48.0 g)
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	5.79 in (14.7 cm)

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Package 2 Width	3.54 in (9.0 cm)
Package 2 Length	5.31 in (13.5 cm)
Package 2 Weight	19.47 oz (552.0 g)
Unit Type of Package 3	CAR
Number of Units in Package 3	200
Package 3 Height	11.42 in (29.0 cm)
Package 3 Width	12.20 in (31.0 cm)
Package 3 Length	18.70 in (47.5 cm)
Package 3 Weight	26.54 lb(US) (12.04 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: carbon black, which is known to the State of California to cause cancer, and Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile

Contractual warranty

Warranty	2 years
----------	---------